



## Socket set 1/4 inch square drive 28 pieces, Type: S



### Order data

Order number	630295 S
GTIN	4013288173836
Item class	63F

### Description

#### Version:

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120**.

#### Application:

For external hexagon screws / nuts with thread M2 – M8 and for hexagon socket head screws with thread M4 – M8.

For Pozidriv and Phillips screws with threads M2 – M6 and internal Torx® screws with thread M3 – M6.

#### Material:

Chrome molybdenum steel, matt chrome-plated.

#### Content:

Size S - with reversible ratchet No. 632295. Size P - With push-through square No. 632290.

#### Supplied with:

Hexagon sockets: 9x; size 5; 5.5; 6; 7; 8; 10; 11; 12; 13 mm

Bits, C 6.3, for hex socket: 4 pcs. No. 675240 size 3; 4; 5; 6

Bits, C 6.3, for Phillips: 3 pcs. No. 675310 size 1/25; 2/25; 3/25

Bits, C 6.3, for Pozidriv: 2 pcs. No. 675320 size 1/25; 2/25

Bits, C 6.3, for internal Torx®: 6 pcs. No. 675340 size TX10; TX15; TX20; TX25; TX27; TX30

Extension with quick-rotation sleeve: 1x 150 mm

Wobble extension: 1x 56 mm

Adapter with quick-change chuck: 1 pc. square socket 1/4 inch – bit holder 1/4 inch

Reversible ratchet (size S): 1 pc. No. 632295

Push-through square ratchet (size P): 1 pc. No. 632290  
Presented in: Textile wallet with hook and loop fastener

## Technical description

Number of pieces	28
Drive profile	Hexagon socket
Drive profile	Screwdriver for Phillips
Drive profile	Hexagon socket
Drive profile	Screwdriver for TORX® screws
Drive profile	Pozidriv screwdriver
Square drive	1/4 in
Width across flats range, hexagon sockets	5-13 mm
Width across flats range, hexagon wrenches	3-6 mm
Manufacturer's designation	8100 SA 8
Packaging	Textile folding wallet, hook and loop fastening
Length	204 mm
Width	91 mm
Height	51 mm
Type of product	Socket spanner

## Accessories

Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm	675320 2/25
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX27	675340 TX27
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 3/25 mm	675310 3/25
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 5 mm	675240 5

Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX15	675340 TX15
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX20	675340 TX20
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX30	675340 TX30
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 4 mm	675240 4
Precision ratchet "Zyklop Metal" reversible, 1/4 inch with ejector	632295
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm	675310 2/25
Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm	675320 1/25
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm	675310 1/25
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX10	675340 TX10
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX25	675340 TX25
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 3 mm	675240 3
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 6 mm	675240 6