



Socket set metric/imperial, 1/2 inch square drive 45 pieces



Order data

| | |
|--------------|---------------|
| Order number | 638810 |
| GTIN | 4018754079445 |
| Item class | 63A |

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**.

Application:

For hexagon head screws / nuts with thread M6 – M22. For hexagon head screws / nuts with thread up to 3/4 inch (American inch size).

Material:

Chrome alloy steel, chrome-plated.

Supplied with:

Bi-hexagon sockets: 22 pcs. No. 642100

size 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 23; 24; 25; 26; 27; 28; 30; 32; 34

Bi-hexagon sockets: 17 pcs. No. 642400

size 3/8; 7/16; 1/2; 9/16; 19/32; 5/8; 11/16; 3/4; 25/32; 13/16; 7/8; 15/16; 1; 1.1/16; 1.1/8; 1.3/16; 1.1/4

T-handle: 1 pc. No. 641300 size 300

Extensions: 3 pcs. No. 641000

size 75; 130; 255

Universal joint: 1 pc. No. 641600 size 1/2

Ratchet: 1 pc. No. 640100 size 1/2

Presented in: Sheet steel case

Technical description

| | |
|---------------|-------------------|
| Drive profile | Bi-hexagon socket |
|---------------|-------------------|

| | |
|--|-------------------|
| Square drive | 1/2 in |
| Number of pieces | 45 |
| Width across flats | metric / imperial |
| Width across flats range, bi-hex sockets | 10-34 mm |
| Width across flats range, bi-hex sockets | 3/8 -1.1/4 in |
| Packaging | Sheet metal case |
| Length | 540 mm |
| Width | 290 mm |
| Height | 53 mm |
| Type of product | Socket spanner |

Accessories

| | |
|--|---------------|
| Bi-hexagon socket, 1/2 inch Width across flats 13/16 in | 642400 13/16 |
| Bi-hexagon socket, 1/2 inch Width across flats 13 mm | 642100 13 |
| Bi-hexagon socket, 1/2 inch Width across flats 24 mm | 642100 24 |
| Bi-hexagon socket, 1/2 inch Width across flats 1.1/16 in | 642400 1.1/16 |
| Extension, 1/2 inch overall length 130 mm | 641000 130 |
| Bi-hexagon socket, 1/2 inch Width across flats 12 mm | 642100 12 |
| Bi-hexagon socket, 1/2 inch Width across flats 17 mm | 642100 17 |
| Bi-hexagon socket, 1/2 inch Width across flats 9/16 in | 642400 9/16 |
| Bi-hexagon socket, 1/2 inch Width across flats 34 mm | 642100 34 |
| Bi-hexagon socket, 1/2 inch Width across flats 25 mm | 642100 25 |
| Bi-hexagon socket, 1/2 inch Width across flats 10 mm | 642100 10 |
| Bi-hexagon socket, 1/2 inch Width across flats 32 mm | 642100 32 |
| Bi-hexagon socket, 1/2 inch Width across flats 18 mm | 642100 18 |
| Bi-hexagon socket, 1/2 inch Width across flats 11 mm | 642100 11 |
| Bi-hexagon socket, 1/2 inch Width across flats 1.1/8 in | 642400 1.1/8 |
| Bi-hexagon socket, 1/2 inch Width across flats 30 mm | 642100 30 |

| | |
|--|---------------|
| Extension, 1/2 inch overall length 255 mm | 641000 255 |
| Bi-hexagon socket, 1/2 inch Width across flats 25/32 in | 642400 25/32 |
| T-handle, 1/2 inch overall length 300 mm | 641300 300 |
| Bi-hexagon socket, 1/2 inch Width across flats 5/8 in | 642400 5/8 |
| Bi-hexagon socket, 1/2 inch Width across flats 16 mm | 642100 16 |
| Bi-hexagon socket, 1/2 inch Width across flats 3/4 in | 642400 3/4 |
| Bi-hexagon socket, 1/2 inch Width across flats 14 mm | 642100 14 |
| Bi-hexagon socket, 1/2 inch Width across flats 7/8 in | 642400 7/8 |
| Bi-hexagon socket, 1/2 inch Width across flats 7/16 in | 642400 7/16 |
| Extension, 1/2 inch overall length 75 mm | 641000 75 |
| Bi-hexagon socket, 1/2 inch Width across flats 1.1/4 in | 642400 1.1/4 |
| Bi-hexagon socket, 1/2 inch Width across flats 21 mm | 642100 21 |
| Bi-hexagon socket, 1/2 inch Width across flats 15 mm | 642100 15 |
| Bi-hexagon socket, 1/2 inch Width across flats 19/32 in | 642400 19/32 |
| Bi-hexagon socket, 1/2 inch Width across flats 1.3/16 in | 642400 1.3/16 |
| Bi-hexagon socket, 1/2 inch Width across flats 3/8 in | 642400 3/8 |
| Bi-hexagon socket, 1/2 inch Width across flats 20 mm | 642100 20 |
| Bi-hexagon socket, 1/2 inch Width across flats 23 mm | 642100 23 |
| Bi-hexagon socket, 1/2 inch Width across flats 19 mm | 642100 19 |
| Bi-hexagon socket, 1/2 inch Width across flats 1/2 in | 642400 1/2 |
| Bi-hexagon socket, 1/2 inch Width across flats 27 mm | 642100 27 |
| Bi-hexagon socket, 1/2 inch Width across flats 28 mm | 642100 28 |
| Universal joint, 1/2 inch Type 1/2 | 641600 1/2 |
| Bi-hexagon socket, 1/2 inch Width across flats 26 mm | 642100 26 |
| Bi-hexagon socket, 1/2 inch Width across flats 22 mm | 642100 22 |
| Bi-hexagon socket, 1/2 inch Width across flats 11/16 in | 642400 11/16 |
| Bi-hexagon socket, 1/2 inch Width across flats 1 in | 642400 1 |
| Bi-hexagon socket, 1/2 inch Width across flats 15/16 in | 642400 15/16 |