



Cordless impact wrench / impact driver, Type: M18FQID



Order data

Order number	074010 M18FQID
GTIN	4002395277636
Item class	03L

Description

Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor**, for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
 - **With overload protection for longer working life of the battery, motor, and gearbox.**
- DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques. **M18 FUEL™ SURGE™ 1/4 inch hex cordless impact driver.**
- **Impact mechanism mounted in an oil bath with FLUID-DRIVE™ technology for very low noise, and extended working life.**
 - **In control step 4 the unit automatically throttles the no-load speed, ideal for instance for self-tapping screws.**

Version of the advertising text:

Robust and **powerful FUEL™ cordless impact screwdriver** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency.

Advantage:

Impact driver with REDLINK PLUS™ electronics.

Supplied with:

Supplied with 2× Li-ion batteries, charger, HD box, belt clip.

Note:

For matching spare batteries and accessories see from No. 073808.

Technical description

Tool arbor size	1/4 in
Number of impacts 2nd stage	0 - 2900 min ⁻¹
maximum screw Ø (8.8 - 12.9)	M14
Tool arbor drive profile	HEX (E 6.3)
Manufacturer's designation	M18FQID-502X
Battery voltage	18 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum vibration to EN	12 m/s ²
Number of impacts 4th setting	0 - 3700 min ⁻¹
maximum torque 1st step	40 Nm
Packaging	Modular case (HD=Heavy Duty)
Battery capacity	5 Ah
Weight	1.8 kg
typical application	Strong
Number of impacts 3rd stage	0 - 3700 min ⁻¹
Type	M18FQID
Number of impacts 1st stage	0 - 1800 min ⁻¹
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

Accessories

Battery charger Type M1218C	073840 M1218C
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218FC	073840 M1218FC