



## Torque shut-off screwdriver with ParameterControl Baton offset screwdriver, Type: 71126260



### Order data

Order number	071120 71126260
GTIN	4014586883830
Item class	03F

### Description

#### Version:

**FEIN ACCU TEC shut-off screwdrivers** are designed for the most demanding applications requiring **precise screw tightening in series production**.

- **Brushless EC motors with working life extended by a factor of several times and up to 80 % lower maintenance costs.**
- **Restart delay after the screw tightening, to avoid "follow-up".**
- **Restart inhibit if the remaining battery charge is insufficient to perform the screw tightening.**
- **Tight screw tightening tolerances for high screw tightening quality.**
- **Precise and consistent tightening torques in any screw tightening application.**
- **Testable screwdrivers, CmK-value > 1.67 ±10% (based on 6 sigma) to ISO 5393 VDI/VDE 2647.**

**The release torque is 25 % above the tightening torque.**

Torque shut-off screwdriver with ParameterControl for easy and individual programming on a PC, using the programming adaptor (No. 071135 size 92604163).

**Freely programmable parameters:** Speed, direction of rotation, angle of rotation, torque threshold and time.

Up to 5 programmable steps. Precise configuration for each screw tightening application. **Final switch-off by mechanical clutch.** Ideal for optimising the process and time.

**Shut-off screwdriver, takes a Li-ion battery. Maintenance-free** up to 500,000 screw fastenings.

**Supplied with:**

Just the screwdriver itself is supplied, **without battery, charger or setting tool and angle head**. Please order the battery, charger, setting tool and angle head specifically for the device.

**Note:**

See No. 073832 ff. for suitable rechargeable batteries and chargers.

See No. 654300 ff. for torque analysers.

See No. 654381 for torque sensors / rotational angle sensors.

Calibration service on request.

## Technical description

Manufacturer's designation	ASW 18-30 PC
Speed range	30 - 420 min <sup>-1</sup>
Weight including rechargeable battery	1.7 kg
Motor design	Brushless EC motor
Torque range	12 - 30 Nm
Battery voltage	12 V
Battery voltage	18 V
Format	Baton offset screwdriver
suitable angle head	071133 15010
suitable battery - supplier / battery type / voltage	Fein type E 12 V
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Screwdriver

## Accessories

ACCU TEC setting tool Type ESTW	071119 ESTW
Electronic torque tool tester "TTT"	654340
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Programming adaptor Type 92604163	071135 92604163

