




## Electrician's screwdriver set, for slot-head, Classic fully insulated, Number of screwdrivers: 6



### Order data

Order number	663010 6
GTIN	7610733064342
Item class	63E

### Description

#### Version:

Handle and blade **fully insulated up to 1000 V to DIN EN IEC 60900 / VDE 0682-201**.

Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

**Slim handle** with a non-allergenic elastomer coating and a core of particularly tough and impact-resistant polypropylene. Due to its special surface structure, the grip is non-slip even with oily or wet hands.

**Blade** of PB Swiss Tools special alloy combines maximum hardness with exceptional toughness. Blades with taper tips, manufactured to the standard dimensions of slots on the screws. Fully insulated, the breakdown strength of the insulation is many times the minimum test voltage set by VDE. Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

#### Application:

For use at voltage up to 1000 V.

Optimum working life for electrician's screwdrivers is assured if screwdrivers always exactly match the standard screw slot size. (see tables part). Incorrect screwdriver size selection will cause damage to the screw head.

#### Content:

1 each screwdriver No. 663000: Size 2.5; 3.5; 4; 5.5; 6.5; 8

### Technical description

Number of screwdrivers	6
Series	Classic VDE

Standard	DIN EN IEC 60900 / VDE 0682-201
Drive profile	Slot-head screwdriver
non-sparking	no
Type of product	Screwdrivers

## Accessories

Electrician's screwdriver for slot-head, Classicfully insulated Blade width b 2 mm	663000 2
Electrician's screwdriver for slot-head, Classicfully insulated Blade width b 10 mm	663000 10
Electrician's screwdriver for slot-head, Classicfully insulated Blade width b 6,5 mm	663000 6,5
Screw holder Type 3	666425 3
Electrician's screwdriver for slot-head, Classicfully insulated Blade width b 3 mm	663000 3
Electrician's screwdriver for slot-head, Classicfully insulated Blade width b 5,5 mm	663000 5,5
Electrician's screwdriver for slot-head, Classicfully insulated Blade width b 4 mm	663000 4
Screw holder Type 2	666425 2
Electrician's screwdriver for slot-head, Classicfully insulated Blade width b 2,5 mm	663000 2,5
Electrician's screwdriver for slot-head, Classicfully insulated Blade width b 3,5 mm	663000 3,5
Electrician's screwdriver for slot-head, Classicfully insulated Blade width b 8 mm	663000 8