




Countersinking bit, single-flute, External Ø: 10,4mm



Order data

Order number	676311 10,4
GTIN	4013288118974
Item class	63H

Description

Version:

1/4 inch hexagon shank to DIN 3126 C 6.3.

CBN ground, single-flute for chatter-free deburring and countersinking.

Advantage:

Quick and uncomplicated changes between drill, countersink and screw bits.

Application:

Ideal for repair and assembly work in mobile situations.

For use in power drills using adapter (No. 675000 – 675050) or in screwdriver holders (No. 676400 – 676770).

Technical description

for countersunk screw	M5
Shaft length	21 mm
overall length	34 mm
for bores from	1.5 mm
Number of cutting edges Z	1
External Ø	10.4 mm
Bit hexagon shank	C 6,3
Manufacturer's designation	845

Tool material	HSS
Countersink tip angle	90 degrees
Type of product	Stepped drill and countersink

Accessories

Kraftform handle, bit holder for 1/4 inch bits C 6.3with magnet Hexagon socket 6,3 mm	676440 6,3
Shank with snap ring Hexagon shank 6,3	675000 6,3
Kraftform handle, bit holder 1/4 inch with telescopic blade	676400
Kraftform screwdriver holder for 1/4 inch bits C 6.3 and E 6.3with quick-change chuck, ESD Hexagon socket 6,3 mm	676415 6,3
Shank with magnet / quick-change coupling Hexagon shank 6,3	675050 6,3
Kraftform screwdriver holder for 1/4 inch bits C 6.3 and E 6.3with quick-change chuck Hexagon socket 6,3 mm	676410 6,3
Bit-holding screwdriver with 1/4 inch bitstelescopic shank and magnet	676555
Shank with quick-change coupling and lock Hexagon shank 6,3	675025 6,3
Kraftform screwdriver holder for 1/4 inch bitswith quick-change chuck Hexagon socket 6,3 mm	676656 6,3
Shank with magnet / quick-change couplingBiTorsion Hexagon shank 6,3	675030 6,3
Kraftform screwdriver holder for 1/4 inch short bits, C 6.3with magnet Hexagon socket 6,3 mm	676405 6,3
Kraftform handle, bit holder for 1/4 inch bits C 6.3with snap ring Hexagon socket 6,3 mm	676420 6,3
Shank with magnet / quick-change coupling Hexagon shank 6,3S	675020 6,3S
Shank with magnet / snap ring Hexagon shank 6,3/150	675015 6,3/150
Shank with magnet / quick-change coupling Hexagon shank 6,3	675020 6,3

Shank with magnet / snap ring Hexagon shank 7-RUND	675010 7-RUND
Shank with magnet / quick-change coupling Hexagon shank 6,3K	675020 6,3K
Shank with magnet / snap ring Hexagon shank 6,3	675015 6,3
Shank with magnet / quick-change coupling Hexagon shank 6,3R	675020 6,3R
Single-handed magazine ratchet with 1/4 inch bits in a textile belt holder	676770