

## Electrician's tool kit, 36 pieces without case



### Order data

Order number	680455
GTIN	2050001017703
Item class	66H

### Description

#### Application:

Contains the most important quality tools for electrical installation work.

#### Content:

**STABILA**® wooden folding rule: 1 pc. No. 466005 size 2

**STABILA**® light metal spirit level: 1 pc. No. 467030 size 400

**PUK**® universal hacksaw: 1 pc. No. 581220

**Wera** slot-head screwdriver, insulated to VDE: 1 pc. each No. 663100 size 3.5; 4; 5.5; 6.5; 8

Voltage tester up to 250 V: 1 pc. No. 665014 size 2.5

Screw-in fuse carrier key to EN 60900, fully insulated up to 1000 V: 1 pc. No. 665800 from 2 - 63 A

**Wera** screwdriver for Phillips, insulated to VDE: 1 pc. each No. 668600 size 1; 2

**KNIPEX**® combination pliers, insulated to VDE: 1 pc. No. 701700 size 160

**KNIPEX**® water pump pliers, insulated to VDE: 1 pc. No. 705740 size 250

**KNIPEX**® snipe nose pliers, insulated to VDE, with side cutter: 1 pc. No. 713300 size 160

**KNIPEX**® side cutter, insulated to VDE: 1 pc. No. 725300 size 160

**KNIPEX**® wire strippers, insulated to VDE: 1 pc. No. 728750 size 160

**JOKARI**® cable stripping knife: 1 pc. No. 728010 size 8 – 28

**RENNSTEIG** stone chisel, flat: 1 pc. No. 742500 size 250

**RENNSTEIG** stone chisel, pointed: 1 pc. No. 742600 size 250

**RENNSTEIG** electrician's chisel, flat: 1 pc. No. 743000 size 250

**GARANT** engineer's hammer with hickory handle: 1 pc. No. 750110 size 500

Club hammer with handle: 1 pc. No. 751010 size 1

**Milwaukee**® carbide concrete drill set in a plastic case: 1 pc. No. 786081 size 5 (Ø 4 – 10 mm)

**PB Swiss Tools** reamer: 1 pc. No. 831700 size 110

**RUNPOTEC®** cable insertion strip made from nylon: 1 pc. No. 814862 size 10

Fixed blade cable knife: 1 pc. No. 844300

Spatula: 1 pc. No. 087650 size 50

Rubber mixing bowl: 1 pc. No. 087680 size 125

Water application brush: 1 pc. No. 087005 size 20

Insulating tape, black: 1 pc. No. 083654 size BLACK

Torch, LED light: 1 pc. No. 081437 size BLACK

**Note:**

**Tools are supplied loose.**

## Technical description

Article no of the battery / rechargeable battery fitted	081557 LR3
Number of batteries contained	3
Power supply	Battery-powered
Type of product	Tool set

## Accessories

Light metal spirit level Length 400 mm	467030 400
Engineer's hammer with handle protection collar Weight without handle 500 g	750110 500
Wire stripping tool chrome-plated VDE insulated overall length 160 mm	728750 160
Stone chisel taper overall length 250 mm	742600 250
LED torch with batteries Colour BLACK	081437 BLACK
Electrician's chisel overall length 250 mm	743000 250
Electrician's screwdriver for Phillips, with Kraftform handle fully insulated Cross-head size 1	668600 1
Scraper, wooden handle Width 50 mm	087650 50
Plaster mixing bowl maximum Ø 125 mm	087680 125
Alligator® water pump pliers VDE grips overall length 250 mm	705740 250
	701700 160

Combination pliers, chrome-platedVDE insulated overall length 160 mm

Insulating tape Colour BLACK	083654 BLACK
Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 4 mm	663100 4
Side cutter, chrome-platedVDE insulated overall length 160 mm	725300 160
General-purpose hacksaw "PUK" with general-purpose blade (310)Fixed handle	581220
Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 6,5 mm	663100 6,5
Fixed blade cable knife	844300
Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 8 mm	663100 8
Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 5,5 mm	663100 5,5
Square reamer with plastic handle Blade length 110 mm	831700 110
Industrial round brush Ø 20 mm	087005 20
Stone chiselflat overall length 250 mm	742500 250
Snipe nose pliers, straightVDE insulated overall length 160 mm	713300 160
Cable stripping knife with hooked blade for cable Ø 8-28 mm	728010 8-28
Electrician's screwdriver for Phillips, with Kraftform handlefully insulated Cross-head size 2	668600 2
Carbide masonry drill set Number of drills 8	786080 8
Screw-in fuse carrier key, dual functionfully insulated	665800
Voltage tester special quality Blade width 2,5 mm	665020 2,5
Nylon cable pulling rod Band length 10 m	814862 10
Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 3,5 mm	663100 3,5
Wooden folding rule, yellow Length 2 m	466005 2