

## Tool set, 29 pieces, tools insulated to VDE in a tool case



### Order data

Order number	680540
GTIN	2050001017611
Item class	66H

### Description

#### Application:

Contains **tools insulated to DIN EN 60900/VDE 0682**. Tool case of smooth synthetic leather.

#### Supplied with:

Single open ended spanner: 1 pc. each No. 613333 size 10; 13; 16; 17; 18; 19

**wiha** socket with handle: 1 pc. each No. 622500 size 5.5; 6; 7; 8; 9; 10

Electrician's slot-head screwdriver: 1 pc. each No. 663301 size 2.5; 3; 3.5; 4; 5.5; 6.5

**PB Swiss Tools** voltage tester up to 250 V: 1 pc. No. 665020 size 2.5

**BENNING** voltage tester "Analog": 1 pc. No. 473105 size ANALOG

Screw-in fuse carrier key, fully insulated up to 1000 V to EN 60900: 1 pc. No. 665800

Electrician's screwdriver for Phillips: 1 pc. each No. 668631 size 1; 2

**KNIPEX**® combination pliers, insulated to VDE: 1 pc. No. 701700 size 180

**KNIPEX**® snipe nose pliers with side cutter: 1 pc. No. 713300 size 200

**KNIPEX**® side cutter, insulated to VDE: 1 pc. No. 725300 size 160

**KNIPEX**® wire strippers, insulated to VDE: 1 pc. No. 728750 size 160

**KNIPEX**® cable cutters: 1 pc. No. 730350 size 165

**KNIPEX**® fixed blade cable knife: 1 pc. No. 844410

#### Note:

**Supplied with tools sorted in a tool case.**

### Technical description

Number of pieces	29
Type of product	tool set

## Accessories

Electrician's screwdriver for slot-headfully insulated Blade width b 3,5 mm	663301 3,5
Nut spinner with handlefully insulated Width across flats 5,5 mm	622500 5,5
Nut spinner with handlefully insulated Width across flats 7 mm	622500 7
Nut spinner with handlefully insulated Width across flats 9 mm	622500 9
Screw-in fuse carrier key, dual functionfully insulated	665800
Single open ended spannerfully insulated Width across flats 18 mm	613330 18
Electrician's screwdriver for Phillipsfully insulated Cross-head size 2	668631 2
Voltage tester special quality Blade width 2,5 mm	665020 2,5
Small cable cutter with 2-component gripsVDE insulated overall length 165 mm	730350 165
Combination pliers, chrome-platedVDE insulated overall length 180 mm	701700 180
Single open ended spannerfully insulated Width across flats 16 mm	613330 16
Snipe nose pliers, straightVDE insulated overall length 200 mm	713300 200
Electrician's screwdriver for slot-headfully insulated Blade width b 6,5 mm	663301 6,5
Single open ended spannerfully insulated Width across flats 13 mm	613330 13
	668631 1

Electrician's screwdriver for Phillips fully insulated Cross-head size 1	
Cable knife fixed fully insulated to VDE	844410
Diagonal side cutter, chrome-plated VDE insulated overall length 160 mm	725300 160
Single open ended spanner fully insulated Width across flats 10 mm	613330 10
Single open ended spanner fully insulated Width across flats 19 mm	613330 19
Nut spinner with handle fully insulated Width across flats 6 mm	622500 6
Electrician's screwdriver for slot-head fully insulated Blade width b 4 mm	663301 4
Voltage tester DUSPOL® Device type ANALOG	473105 ANALOG
Wire stripping tool chrome-plated VDE insulated overall length 160 mm	728750 160
Single open ended spanner fully insulated Width across flats 17 mm	613330 17
Nut spinner with handle fully insulated Width across flats 10 mm	622500 10
Nut spinner with handle fully insulated Width across flats 8 mm	622500 8
Electrician's screwdriver for slot-head fully insulated Blade width b 5,5 mm	663301 5,5
Electrician's screwdriver for slot-head fully insulated Blade width b 2,5 mm	663301 2,5
Electrician's screwdriver for slot-head fully insulated Blade width b 3 mm	663301 3
Voltage tester DUSPOL® Device type ANALOG	473106 ANALOG
Tool case with zip fastening and centre partition	691538