




## Countersinking bit, three-flute, External Ø: 12,4mm



### Order data

Order number	676310 12,4
GTIN	4013288101471
Item class	63H

### Description

**Version:**

1/4 inch hexagon shank to DIN 3126 C 6.3.

**Advantage:**

Quick and uncomplicated changes between drill, countersink, and screw bits.

**Application:**

Ideal for repair and assembly work in mobile situations.

For use in power drills using adapter (No. 675000 – 675050) or in screwdriver holders (No. 676400 – 676770).

### Technical description

for countersunk screw	M6
overall length	35 mm
for bores from	2.8 mm
Shaft length	20 mm
Number of cutting edges Z	3

External Ø	12.4 mm
Bit hexagon shank	C 6,3
Manufacturer's designation	846 HSS
Tool material	HSS
Countersink tip angle	90 degrees
Standard	DIN 335 C
Type of product	Stepped drill and countersink

## Accessories

Kraftform screwdriver holder for 1/4 inch bits C 6.3 and E 6.3 with quick-change chuck, ESD Hexagon socket 6,3 mm	676415 6,3
Kraftform handle, bit holder for 1/4 inch bits C 6.3 with magnet Hexagon socket 6,3 mm	676440 6,3
Shank with quick-change coupling and lock Hexagon shank 6,3	675025 6,3
Shank with snap ring Hexagon shank 6,3	675000 6,3
Kraftform handle, bit holder 1/4 inch with telescopic blade	676400
Kraftform screwdriver holder for 1/4 inch bits with quick-change chuck Hexagon socket 6,3 mm	676656 6,3
Kraftform screwdriver holder for 1/4 inch short bits, C 6.3 with magnet Hexagon socket 6,3 mm	676405 6,3
Shank with magnet / quick-change coupling Hexagon shank 6,3S	675020 6,3S
Shank with magnet / quick-change coupling BiTorsion Hexagon shank 6,3	675030 6,3
Kraftform handle, bit holder for 1/4 inch bits C 6.3 with snap ring Hexagon socket 6,3 mm	676420 6,3
Kraftform screwdriver holder for 1/4 inch bits C 6.3 and E 6.3 with quick-change chuck Hexagon socket 6,3 mm	676410 6,3
Shank with magnet / snap ring Hexagon shank 6,3	675015 6,3
	676770

Single-handed magazine ratchet with 1/4 inch bits in a textile belt holder

Shank with magnet / quick-change coupling Hexagon shank 6,3R

675020 6,3R

Shank with magnet / snap ring Hexagon shank 6,3/150

675015 6,3/150

Shank with magnet / quick-change coupling Hexagon shank 6,3

675020 6,3

Shank with magnet / snap ring Hexagon shank 7-RUND

675010 7-RUND

Shank with magnet / quick-change coupling Hexagon shank 6,3

675050 6,3

Bit-holding screwdriver with 1/4 inch bitstelescopic shank and magnet

676555

Shank with magnet / quick-change coupling Hexagon shank 6,3K

675020 6,3K