

Garant
Bit set with drive tool 32 pieces

Order data

| | |
|--------------|---------------|
| Order number | 676160 |
| GTIN | 4045197635013 |
| Item class | 61F |

Description
Version:

System box of virtually indestructible ABS plastic with integral hinges and snap fastener. The bits are widely spaced so that when the box is open they can be easily accessed and taken out.

Practical Kraftform Kompakt® set of bits and drive tool **for manual and machine drives.**

Kraftform handle with quick-change holder for 1/4 inch bits with C 6.3 **and** E 6.3 shank.

Content:

Assorted bits C 6.3 (1/4 inch); 1 coupling shank; 1 adaptor; 1 bit ratchet

Content:

Bits, length 25 mm, C 6.3, for Phillips: No. 675105 1 pc. each size 1/25; 2/25; 3/25

Bits, length 25 mm, C 6.3, for Pozidriv: No. 675115 2 pcs. each size 1/25; 2/25; 3/25

Bits, length 25 mm, C 6.3, for hex socket: No. 675125 1 pc. size 2.5; 3; 4; 5; 6

Bits, length 25 mm, C 6.3, for internal Torx®: No. 675155 2 pcs. each size TX10; TX15; TX20; TX25; TX30; TX40

Bits, length 25 mm, C 6.3, for slot-head: 1 pc. size 4×0.5; 5.5×1; 6.5×1.2

adapter: 1 pc. 1/4 inch square socket – 1/4 inch bit holder

Quick-release adaptor: 1 pc. No. 675050 size 6.3

Bit ratchet, 1/4 inch: 1 pc. No. 676690

Technical description

| | |
|-------------------|------------------------------|
| Bit hexagon shank | C 6,3 |
| Height | 47 mm |
| Length | 127 mm |
| Width | 85 mm |
| Drive profile | Screwdriver for TORX® screws |
| Drive profile | Screwdriver for Phillips |
| Drive profile | Pozidriv screwdriver |
| Drive profile | Slot-head screwdriver |
| Drive profile | Hexagon screwdriver |
| Number of pieces | 32 |
| Drive tool | Bit ratchet, 1/4 inch |
| Packaging | ABS plastic box |
| Type of product | Bit tool |

Accessories

| | |
|--|-------------|
| Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 3 mm | 675125 3 |
| Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 6 mm | 675125 6 |
| Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 4 mm | 675125 4 |
| Modular box Type 21-1 | 630320 21-1 |
| Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 1/25 mm | 675115 1/25 |
| Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 3/25 mm | 675105 3/25 |
| Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX20 | 675155 TX20 |
| Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 2/25 mm | 675115 2/25 |

| | |
|--|-------------|
| Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 2,5 mm | 675125 2,5 |
| Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX30 | 675155 TX30 |
| Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 2/25 mm | 675105 2/25 |
| Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX25 | 675155 TX25 |
| Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 5 mm | 675125 5 |
| Ratchet bit holder for 1/4 inch bits C 6.3 and E 6.3 Type 1/4 | 676690 1/4 |
| Shank with magnet / quick-change coupling Hexagon shank 6,3 | 675050 6,3 |
| Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX10 | 675155 TX10 |
| Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 1/25 mm | 675105 1/25 |
| Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX15 | 675155 TX15 |
| Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 3/25 mm | 675115 3/25 |
| Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX40 | 675155 TX40 |