



## Jobber drill bit set in a tool roll, for wood, 15 pieces



### Order data

Order number	676317
GTIN	9002696324652
Item class	66B

### Description

**Version:**

1/4 inch hexagon shank to DIN 3126 C 6.3.

**Advantage:**

Quick and uncomplicated changes between drill, countersink, and screw bits.

**Application:**

Ideal for repair and assembly work in mobile situations.

**Content:**

Wood jobber drill bits: No. 676315 1 pc. each size 3; 4; 5; 6; 8

Bits for Pozidriv: 1 pc. each size 1/25; 2/25; 3/25

Bits for internal Torx®: 1 pc. each size TX10; TX15; TX20; TX25; TX30; TX40

Quick-change adaptor: 1 pc. similar to No. 675020 size 6.3K (with magnet)

### Technical description

Number of drills	5
Number of pieces	15
Drive profile	Pozidriv screwdriver

Drive profile	Screwdriver for TORX® screws
Tool material	HSS
Type of product	Jobber drill bit

## Accessories

Jobber drill bit, for wood Drill Ø 8 mm	676315 8
PrecisionBit for Torx®, 1/4 inch C 6.3 Torx® profile TX20	675295 TX20
Shank with magnet / quick-change coupling Hexagon shank 6,3K	675020 6,3K
Jobber drill bit, for wood Drill Ø 10 mm	676315 10
PrecisionBit for Torx®, 1/4 inch C 6.3 Torx® profile TX25	675295 TX25
PrecisionBit for Torx®, 1/4 inch C 6.3 Torx® profile TX30	675295 TX30
Jobber drill bit, for wood Drill Ø 4 mm	676315 4
Jobber drill bit, for wood Drill Ø 3 mm	676315 3
Jobber drill bit, for wood Drill Ø 6 mm	676315 6
PrecisionBit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 3/25 mm	675285 3/25
Jobber drill bit, for wood Drill Ø 5 mm	676315 5
PrecisionBit for Torx®, 1/4 inch C 6.3 Torx® profile TX10	675295 TX10
PrecisionBit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm	675285 1/25
PrecisionBit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm	675285 2/25
PrecisionBit for Torx®, 1/4 inch C 6.3 Torx® profile TX40	675295 TX40
PrecisionBit for Torx®, 1/4 inch C 6.3 Torx® profile TX15	675295 TX15