

Trainee electronics fitter's tool kit, 25 pieces with tool case



Order data

Order number	680440
GTIN	2050001017581
Item class	66H

Description

Application:

Contains a high quality basic tool set for trainee electrical fitters, based on the existing workshop tool set.

Supplied with:

GARANT calipers: 1 pc. No. 410100 size 150

STABILA® wooden folding rule: 1 pc. No. 465960 size 2

DICK half-round file: 1 pc. No. 513300 size 250

Hardwood file handle: 1 pc. No. 519400 size 120

PUK® universal hacksaw: 1 pc. No. 581220 size 150

Wera slot-head screwdriver, insulated to VDE: 1 pc. each No. 663100 size 2.5; 3.5; 4; 5.5; 6.5; 8

Wera screwdriver for Phillips, insulated to VDE: 1 pc. each No. 668600 size 1; 2

KNIPEX® combination pliers, insulated to VDE: 1 pc. No. 701700 size 160

KNIPEX® water pump pliers, insulated to VDE: 1 pc. No. 705740 size 250

KNIPEX® flat-nose pliers, insulated to VDE: 1 pc. No. 710300 size 160

KNIPEX® round-nose pliers, insulated to VDE: 1 pc. No. 710700 size 160

KNIPEX® snipe nose pliers, insulated to VDE: 1 pc. each No. 713300 size 160; 200

GARANT electronics side cutter: 1 pc. No. 726210 size 125

JOKARI® automatic wire strippers: 1 pc. No. 728622 size 6

JOKARI® sheath and wire stripper for all common coaxial cables: 1 pc. No. 729806 size RG58/59

GARANT engineer's hammer with hickory handle: 1 pc. No. 750110 size 300

Plastic hammer: 1 pc. No. 754200 size 32

Cable knife with wooden handle, folding: 1 pc. No. 844500 size 1

PARAT® tool case: 1 pc. No. 690200

Note:

Tool is supplied loose.

Technical description

Type of product

tool set

Accessories

Flat nose pliers chrome-platedVDE insulated overall length 160 mm

710300 160

Round nose pliers chrome-platedVDE insulated overall length 160 mm

710700 160

Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 8 mm

663100 8

Wire stripping tool, economy version for conductor cross-section 6 mm²

728622 6

Electronics side cutter, standard head shape Overall length 125 mm

726210 125

Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 3,5 mm

663100 3,5

Cable knife with wooden handle, folding Type 1

844500 1

Wooden folding rule white Length 2 m

465950 2

Electrician's screwdriver for Phillips, with Kraftform handlefully insulated Cross-head size 1

668600 1

Engineer's hammer withhandle protection collar Weight without handle 300 g

750110 300

Snipe nose pliers, straightVDE insulated overall length 160 mm

713300 160

General-purpose hacksaw "PUK" with general-purpose blade (310)Fixed handle

581220

Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 2,5 mm	663100 2,5
Alligator® water pump pliersVDE grips overall length 250 mm	705740 250
Combination pliers, chrome-platedVDE insulated overall length 160 mm	701700 160
Half round file Length without tang 250 mm	513300 250
Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 4 mm	663100 4
Leather tool case with centre partition	690200
Electrician's screwdriver for Phillips, with Kraftform handlefully insulated Cross-head size 2	668600 2
Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 6,5 mm	663100 6,5
Vernier caliper Measuring range 150 mm	410100 150
Plastic hammer with polyurethane inserts Hammer head Ø 32 mm	754200 32
Round coaxial cable stripping tool for coaxial cable types RG58/59	729806 RG58/59
Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 5,5 mm	663100 5,5
Hardwood file handle Overall length 120 mm	519400 120
Snipe nose pliers, straightVDE insulated overall length 200 mm	713300 200
Trainee electronics fitter's tool kit, 25 pieceswithout tool case	680445