



## Socket set 1/4 inch square drive 41 pieces, Type: 6

### Order data

Order number	630325 6
GTIN	4045197997012
Item class	61A

### Description

#### Version:

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120.**

System box of virtually indestructible ABS plastic with integral hinges and innovative, easy-to-use snap fastener. All tools are held securely for easy access in a specially moulded **PUR foam insert.**

The Surface Drive profile works directly on the faces of the nuts and bolts; weaker corners are protected. Even intermediate sizes (e.g. inch size bolts) and worn bolt heads can be tightened or released using the Surface Drive profile. The Wobble-Fix extensions allow use at an angle and can be secured by clicking into place.

#### Application:

For nuts / bolts gs\_profil\_6kant-einsatz M2–M8 and for hexagon socket head screws gs\_profil\_6kant M4–M10.

For cross-head screws gs\_profil\_phillips gs\_profil\_pozidriv M2–M6, slot-head screws gs\_profil\_schlitz M2–M4

for internal Torx® screws gs\_profil\_torx M2.5–M8

#### Material:

Chrome vanadium steel, chrome-plated.

#### Supplied with:

Surface Drive hexagon sockets: 13 pcs. No. 631225 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14

Hexagon BITS C 6.3: 4 pcs. similar to No. 675240 size 3; 4; 5; 6

BITS for Phillips C6.3: 3 pcs. similar to No. 675310 size 1/25; 2/25; 3/25

Pozidriv BITS C6.3: 3 pcs. similar to No. 675320 size 1/25; 2/25; 3/25

Schlitz BITS C 6.3: 3 pcs. similar to No. 675250 size 3.5×0.6; 5.5×0.8; 8×1.2

BITS for Torx® C 6.3: 6 pcs. similar to No. 675340 size TX10; TX15; TX20; TX25; TX30; TX40

T-handle: 1 pc. No. 633029

Spinner handle "Wobble-Fix": 1 pc. similar to No. 632829

"Wobble-Fix" extensions: 2 pcs. similar to No. 632525 size 50; 100

Universal joint: 1 pc. No. 633529

Ratchet: 1 pc. No. 632025 with ejector

Adaptor E 6.3: 1 pc. similar to No. 675020 size 6.3K for 1/4 inch BITS C 6.3

Converter: 1 pc. similar to No. 650005 size 2 gs\_profil\_6kant-kupplung E 6.3 1/4 inch - ■ 1/4 inch

Bit adapter: 1 pc. similar to No 676800 1/4 inch gs\_profil\_4kant-einsatz - gs\_profil\_6kant-schluesselfilfe 1/4 inch

Presented in: ABS plastic box

Hexagon socket profile: Surface drive

Square with Wobble-Fix: with angle of inclination

Degree of fill of a drawer in units: 5×10

Length: 255 mm

Width: 145 mm

Height: 45 mm

Square drive: 1/4 inch

Width across flats range, Surface Drive: 4-14 mm

Width across flats range, hexagon wrenches: 3-6 mm

## Technical description

with QuickRelease	
Material	
Surface	
Square with Wobble-Fix	with angle of inclination
Norm	
Packaging	ABS plastic box with quick release fastener.
Hexagon socket profile	Surface drive
Width	147 mm
Length	257 mm
Height	45 mm
Degree of fill of a drawer in units	5×10
Type of product	