



Torque shut-off screwdriver with ParameterControl Baton offset screwdriver, Type: 71127060



Order data

Order number	071120 71127060
GTIN	4014586888002
Item class	03F

Description

Version:

FEIN ACCU TEC shut-off screwdrivers are designed for the most demanding applications requiring **precise screw tightening in series production**.

- **Brushless EC motors with working life extended by a factor of several times and up to 80 % lower maintenance costs.**
- **Restart delay after the screw tightening, to avoid "follow-up".**
- **Restart inhibit if the remaining battery charge is insufficient to perform the screw tightening.**
- **Tight screw tightening tolerances for high screw tightening quality.**
- **Precise and consistent tightening torques in any screw tightening application.**
- **Testable screwdrivers, CmK-value > 1.67 ±10% (based on 6 sigma) to ISO 5393 VDI/VDE 2647.**

The release torque is 25 % above the tightening torque.

Torque shut-off screwdriver with ParameterControl for easy and individual programming on a PC, using the programming adaptor (No. 071135 size 92604163).

Freely programmable parameters: Speed, direction of rotation, angle of rotation, torque threshold and time.

Up to 5 programmable steps. Precise configuration for each screw tightening application. **Final switch-off by mechanical clutch.** Ideal for optimising the process and time.

Shut-off screwdriver, takes a Li-ion battery. Maintenance-free up to 500,000 screw fastenings.

Supplied with:

Just the screwdriver itself is supplied, **without battery, charger or setting tool and angle head**. Please order the battery, charger, setting tool and angle head specifically for the device.

Note:

See No. 073832 ff. for suitable rechargeable batteries and chargers.

See No. 654300 ff. for torque analysers.

See No. 654381 for torque sensors / rotational angle sensors.

Calibration service on request.

Technical description

Speed range	65 - 900 min ⁻¹
suitable battery - supplier / battery type / voltage	Fein type E 12 V
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Format	Baton offset screwdriver
Type of rechargeable battery	Lithium-ion
Weight including rechargeable battery	1.2 kg
Manufacturer's designation	ASW 18-18 PC
Battery voltage	12 V
Battery voltage	18 V
Motor design	Brushless EC motor
suitable angle head	071133 17010
Torque range	6 - 18 Nm
Power supply	Rechargeable battery-powered
Type of product	Screwdriver

Accessories

ACCU TEC setting tool Type ESTW	071119 ESTW
Angle head for ASW 18 Type 21020	071133 21020
Electronic torque screwdriver tester "TST" maximum torque 25 N·m	654300 25
Electronic torque tool tester "TTT"	654340

Angle head for ASW 18 Type 18020	071133 18020
Programming adaptor Type 92604163	071135 92604163
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18