



Electrician's competence toolbox XXL II 115 items, Type: 2



Order data

Order number	680525 2
GTIN	4010995420697
Item class	60N

Description

Version:

Comprehensive electrician's tool kit in a impact-resistant case of polypropylene. The gas pressure dampers additionally fitted hold the cover in different positions and prevent it falling closed automatically.

Supplied with:

TorqueVario®-S electric torque screwdriver set: 18-piece, 0.5–5.0 Nm
 LiftUp electric, PH; PZ; PlusMinus screwdriver with bit magazine: 7 items
 SoftFinish® electric slimVario screwdriver with bit holder for 6 mm slimBits: 1 pc.
 SlimBit electric bit, PZ: 1 pc. size 2
 SoftFinish® electric slimFix screwdriver for slot-head screws: 1 pc. each size 3.5; 5.5; 6.5
 SoftFinish® electric slimFix, PH screwdriver: 1 pc. each size 1; 2
 SoftFinish® electric slimFix, PZ screwdriver: 1 pc. each size 1; 2
 SoftFinish® electric slimFix, PZ PlusMinus screwdriver: 1 pc. each size 1; 2
 SoftFinish® electric slimFix screwdriver for Torx® Tamper Resistant: 1 pc. each size 10; 15; 20; 25
 SoftFinish® electric screwdriver for external hex-head bolts: 1 pc. each size 5.5; 7; 8; 10; 13
 PicoFinish electric, PH precision screwdriver: 1 pc. size 0
 PicoFinish electric precision screwdriver for slot-head screws: 1 pc. size 2.5
 Universal control cabinet key, external square 5–8, external triangle 9: 1 pc.
 SoftFinish® screwdriver, for slot-head screws: 1 pc. each size 3.5; 12
 XLSelector Y-Bit 25 mm bit set: 31-piece

Set of hexagon key L-wrenches with ball point in ErgoStar holder, for hexagonal socket screws: 9-piece

High-performance BiCut® Professional side cutters with DynamicJoint®: 1 pc.

Professional electric side cutters with DynamicJoint®: 1 pc.

Professional electric cable cutters: 1 pc.

Classic precision diagonal side cutters: 1 pc.

Professional electric combination pliers with DynamicJoint® and OptiGrip: 1 pc.

Professional electric snipe nose pliers, angled 40°: 1 pc.

Professional electric snipe nose pliers, straight: 1 pc.

Professional electric water pump pliers: 1 pc.

TriCut Professional electric installation pliers: 1 pc.

Cable stripping tool: 1 pc.

Automatic wire strippers for 0.03–16 mm²: 1 pc.

Automatic crimping tool for terminal sleeves 0.08 – 16 mm²: 1 pc.

Crimping tool for insulated cable lugs and contacts 0.5–6 mm²: 1 pc.

Electrician's shears for cables up to 50 mm² and crimp function for terminal sleeves 1–5 mm²: 1 pc.

Voltage tester, non-contact, single phase, 230–1000 V AC: 1 pc.

SoftFinish® voltage tester, single phase, 110-250 V AC, slot-head: 1 pc. size 3

LED torch max. 300 lm, with laser class 2 and UV light max. 400 nm: 1 pc.

Electrician's spirit level, length 400 mm: 1 pc.

Electrician's Longlife® folding rule, length 2 m, orange: 1 pc.

SoftFinish® wall plug punch, with wall plugs: 5-piece

Electrician's hammer, 300 g: 1 pc.

Note:

Supplied loose.

Technical description