

**Garant**
**Socket set 1/4 inch square drive 39 pieces, Type: 6**

**Order data**

Order number	630299 6
GTIN	4062406060275
Item class	61A

**Description**
**Version:**

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120.**

System box of virtually indestructible ABS plastic with integral hinges and innovative, easy-to-use snap fastener.

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay.**

**Application:**

For external hexagon screws / nuts with thread M2 – M8

and for hexagon socket head screws with thread M4 – M10.

For Pozidriv and Phillips screws with thread M2 – M6, slot-head screws with thread M2 – M4

and for internal Torx® screws with thread M2.5 – M8.

**Material:**

Chrome vanadium steel, chrome-plated.

**Supplied with:**

Sockets single hexagon: 12 pcs. No. 631029 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13

Bits, C 6.3, for hex socket: 5 pcs. similar to No. 675240 size 3; 4; 5; 6; 8

Bits, C 6.3, for Phillips: 3 pcs. similar to No. 675310 size 1, 2; 3

Bit, C 6.3, for Pozidriv: 1 pc. similar to No. 675320 size 2

Bits, C 6.3, for slot-head: 4 pcs. similar to No. 675250 size 3; 4; 5.5; 6.5

Bits, C 6.3, for internal Torx®: 8 pcs. similar to No. 675340 size TX8; TX9; TX10; TX15; TX20; TX25; TX30; TX40

Holder for bits: 1 pc. similar to No. 676800 size 4/4

Spinner handle: 1 pc. No. 632829 size 146  
 Extensions: 2 pcs. No. 632429 size 50; 100  
 Universal joint: 1 pc. No. 633529 size 1/4  
 Ratchet: 1 pc. No. 632025 size 1/4  
 Storage in: ABS plastic box  
 Degree of fill of a drawer in units: 5×10  
 Height: 45 mm  
 Square drive: 1/4 in  
 Width across flats range, hexagon sockets: 4-13 mm  
 Width across flats range, hexagon wrenches: 3-8 mm

## Technical description

Width across flats range, hexagon wrenches	3-8 mm
Drive profile	Hexagon socket
Drive profile	Hexagon screwdriver
Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver
Drive profile	Slot-head screwdriver
Drive profile	Screwdriver for TORX® screws
Width across flats range, hexagon sockets	4-13 mm
Square drive	1/4 in
Packaging	ABS plastic box with quick release fastener.
Length	257 mm
Width	147 mm
Height	45 mm
Degree of fill of a drawer in units	5×10
Type of product	Socket spanner

## Accessories

Extension, 1/4 inch overall length 50 mm	632429 50
--	-----------

Hexagon socket, 1/4 inch Width across flats 6 mm	631029 6
Spinner handle, 1/4 inch overall length 146 mm	632829 146
Hexagon socket, 1/4 inch Width across flats 4 mm	631029 4
Hexagon socket, 1/4 inch Width across flats 9 mm	631029 9
Modular box Type 2	630305 2
Hexagon socket, 1/4 inch Width across flats 4,5 mm	631029 4,5
PUR foam inlay for set 630299	630304 630299
Hexagon socket, 1/4 inch Width across flats 12 mm	631029 12
Hexagon socket, 1/4 inch Width across flats 10 mm	631029 10
Hexagon socket, 1/4 inch Width across flats 5 mm	631029 5
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631029 5,5
Reversible ratchet, 1/4 inch with ejector Type	632025
Hexagon socket, 1/4 inch Width across flats 8 mm	631029 8
Extension, 1/4 inch overall length 100 mm	632429 100
Hexagon socket, 1/4 inch Width across flats 13 mm	631029 13
Universal joint 1/4 inch Type 1/4	633529 1/4
Hexagon socket, 1/4 inch Width across flats 11 mm	631029 11
Hexagon socket, 1/4 inch Width across flats 7 mm	631029 7