

Garant
Socket set 3/8 inch square drive 25 pieces, Type: 6

Order data

Order number	634312 6
GTIN	4062406060763
Item class	61A

Description
Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**.

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay**. With hexagon sockets No. 637229.

Application:

For hexagon head screws / nuts with thread M5 – M12, for spark plugs and for hexagon socket head screws with thread M4 – M12.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Sockets bi-hexagon or single hexagon: 11 pcs. size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19 mm

Spark plug sockets: 2 pcs. No. 637329 size 16; 20.8

Hexagon screwdriver bits: 7 pcs. No. 637629 size 3; 4; 5; 6; 7; 8; 10

T-handle: 1 pc. No. 635729

Extensions: 2 pcs. No. 635429 size 75; 240

Universal joint: 1 pc. No. 636229

Ratchet: 1 pc. No. 635025

Storage in: ABS plastic box

Degree of fill of a drawer in units: 6x14

Height: 45 mm

Square drive: 3/8 inch

Width across flats range, hexagon sockets: 8-19 mm

Width across flats range, hexagon wrenches: 3-10 mm

Technical description

Width across flats range, hexagon sockets	8-19 mm
Width across flats range, hexagon wrenches	3-10 mm
Drive profile	Hexagon screwdriver
Drive profile	Hexagon socket
Square drive	3/8 inch
Packaging	ABS plastic box
Length	357 mm
Width	176 mm
Height	45 mm
Degree of fill of a drawer in units	6×14
Type of product	Socket spanner

Accessories

Single hexagon socket for spark plugs 3/8 inch Width across flats 16 mm	637329 16
Extension, 3/8 inch overall length 240 mm	635429 240
T-handle, 3/8 inch overall length 200 mm	635729 200
Universal joint 3/8 inch Type 3/8	636229 3/8
Reversible ratchet, 3/8 inch with ejector Type	635025
Hexagon screwdriver bit 3/8 inch Hexagon 7 mm	637629 7
Hexagon screwdriver bit 3/8 inch Hexagon 10 mm	637629 10
Hexagon screwdriver bit 3/8 inch Hexagon 4 mm	637629 4
Single hexagon socket for spark plugs 3/8 inch Width across flats 20,8 mm	637329 20,8
Extension, 3/8 inch overall length 75 mm	635429 75
Hexagon screwdriver bit 3/8 inch Hexagon 6 mm	637629 6

Hexagon screwdriver bit 3/8 inch Hexagon 3 mm	637629 3
Hexagon screwdriver bit 3/8 inch Hexagon 5 mm	637629 5
Hexagon screwdriver bit 3/8 inch Hexagon 8 mm	637629 8
Modular box Type 3A	630305 3A
PUR foam inlay for set 634312	630304 634312