

Garant GRIDLINE

Auxiliary cabinet with cupboard and 3 drawers, Height mm: 1000**Order data**

Order number	932010 1000
GTIN	4062406066260
Item class	9GK

Description**Version:**

Tool auxiliary cabinet in 24×28G, with drawers 20×24G. Cupboard with door and storage shelf, adjustable in 25 mm intervals. Door separately lockable by push handle with cylinder lock. With 3 drawers, can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Drawer usable area in G: 20×24

Height: 1000 mm

Width: 600 mm

Depth: 700 mm

Usable height: 900 mm

Drawer usable width: 500 mm

Drawer usable depth: 600 mm

Technical description

Drawer usable width	500 mm
Ribbed rubber inlay with anti-roll lip on 3 sides	no
Drawer usable depth	600 mm
Width	600 mm
Drawer usable depth in G	24
Door stop	right-hand
Drawer usable area in G	20×24
Depth	700 mm
Usable height	900 mm
Weight	89 kg
Electronic locking system can be retrofitted	yes
Drawer usable width in G	20
Number of drawers	3
Height	1000 mm
ComfortClose	no
Door height	600 mm
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Shelf load capacity / maximum distributed shelf load (on metal)	80 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×24G

Type of product	Machine auxiliary cabinet
-----------------	---------------------------

Accessories

Storage shelf Type 1	932025 1
Pull-out shelf 75 kg Type 75	932035 75
Drawer, 75 kg Drawer front height 100 mm	931043 100
Drawer, 75 kg Drawer front height 150 mm	931043 150
Drawer, 75 kg Drawer front height 50 mm	931043 50
Slide handle for GridLine Type HU12	914226 HU12
Lock plate for GridLine Type HU21	914227 HU21
easyPick small parts storage bins set Drawer front height / type 50/1	950450 50/1
easyPick small parts storage bins set Drawer front height / type 50/2	950450 50/2
easyPick small parts storage bins set Drawer front height / type 50/3	950450 50/3
Set of troughs Drawer front height / type 50/1	950460 50/1
Set of troughs Drawer front height / type 50/2	950460 50/2
Slotted / plain divider sets Drawer front height / type 100/1	950470 100/1
Slotted / plain divider sets Drawer front height / type 100/2	950470 100/2
Slotted / plain divider sets Drawer front height / type 100/3	950470 100/3
Mat for drawers Dimension in G 20X24	951830 20X24
Non-slip mats set for drawers, 5 pieces Dimension in G 20X24	951885 20X24
Ribbed rubber mat for drawers Dimension in G 20X24	951910 20X24
Measuring tools set Number of tools 7	952048 7
Measuring tools set Number of tools 8	952083 8

Workshop file set Number of tools 7	952263 7
Open-ended / ratchet ring spanner set Number of tools 11	952365 11
Combination spanner set Number of tools 19	952452 19
Open ended spanner set Number of tools 11	952523 11
Double-ended ring spanner set Number of tools 11	952525 11
Open ended spanner set Number of tools 12	952535 12
Nut spinner set Number of tools 9	952625 9
Nut spinner set Number of tools 12	952752 12
Hexagon screwdriver set with T-handle Number of tools 9	953035 9
Screwdriver set for Torx® Number of tools 9	953115 9
Screwdriver set for Torx®, with T-handle Number of tools 9	953120 9
Screwdriver set Number of tools 11	953201 11
Screwdriver set Number of tools 31	953201 31
Torx® screwdriver set with T-handle Number of tools 15	953285 15
Screwdriver set Number of tools 10	953370 10
Screwdriver set Number of tools 9	953372 9
Screwdriver set Number of tools 17	953551 17
Socket set 1/2 inch Number of tools 32	953857 32
Socket set 1/2 inch and 1/4 inch Number of tools 41	953860 41
Pliers set Number of tools 5	954231 5
Screwdriver set, fully insulated Number of tools 9	954495 9
Electrician's tool set, fully insulated Number of tools 12	954585 12
Hammer set Number of tools 3	954672 3
Workshop accessories assortment Number of tools 9	954986 9
Marking out and sawing Number of tools 8	954987 8