


**Garant**
**Socket set 1/4; 1/2 inch square drive 38 pieces, Type: 6**

**Order data**

Order number	630012 6
GTIN	4062406060213
Item class	61A

**Description**
**Version:**

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120.**

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay.**

**Application:**

For external hexagon screws / nuts with thread M2 – M20.

For hexagon socket head screws with thread M4 – M18.

**Material:**

Chrome vanadium steel, chrome-plated.

**Supplied with:**

1/4 inch hexagon socket set: 9 pcs. No. 631029 size 4; 5; 5.5; 6; 7; 8; 9; 10; 11

1/2 inch hexagon socket set: 10 pcs. No. 642229 size 13; 16; 17; 18; 19; 21; 22; 24; 27; 30

1/4 inch hexagon screwdriver bits: 3 pcs. No. 631729 size 3; 4; 5

1/2 inch hexagon screwdriver bits: 5 pcs. No. 643229 size 6; 8; 10; 12; 14

1/4 inch tommy-bar: 1 pc. No. 633029 size 116

1/2 inch tommy-bar: 1 pc. No. 641329 size 295

1/4 inch spinner handle: 1 pc. No. 632829 size 1/4

1/4 inch extensions: 2 pcs. No. 632429 size 50; 150

1/2 inch extensions: 2 pcs. No. 641029 size 130; 255

1/4 inch universal joint: 1 pc. No. 633529 size 1/4

1/2 inch universal joint: 1 pc. No. 641629 size 1/2

1/4 inch ratchet: 1 pc. No. 632025 size 1/4

1/2 inch ratchet: 1 pc. No. 640025 size 1/2

Storage in: ABS plastic box

**Note:**

The range offers in addition space for 4 pieces of small parts storage bins No. 951251 size 2x3/1 (not included in the scope of supply).

## Technical description

Square drive	1/2 in
Square drive	1/4 in
Width across flats range, hexagon sockets	4-30 mm
Number of pieces	38
Drive profile	Hexagon screwdriver
Drive profile	Hexagon socket
Width across flats range, hexagon wrenches	3-14 mm
Packaging	ABS plastic box
Length	510 mm
Width	294 mm
Height	61 mm
Degree of fill of a drawer in units	8x20
Type of product	Socket spanner

## Accessories

Hexagon bit socket, 1/2 inch Hexagon 10 mm	643229 10
T-handle, 1/4 inch overall length 116 mm	633029 116
Hexagon socket, 1/4 inch Width across flats 6 mm	631029 6
Extension, 1/2 inch overall length 255 mm	641029 255
Hexagon bit socket, 1/4 inch long Hexagon 3 mm	631729 3
Spinner handle, 1/4 inch overall length 146 mm	632829 146
Hexagon socket, 1/2 inch Width across flats 21 mm	642229 21
Universal joint 1/4 inch Type 1/4	633529 1/4

Hexagon bit socket, 1/2 inch Hexagon 14 mm	643229 14
Hexagon bit socket, 1/2 inch Hexagon 6 mm	643229 6
Hexagon socket, 1/4 inch Width across flats 10 mm	631029 10
Hexagon socket, 1/2 inch Width across flats 22 mm	642229 22
PUR foam inlay for set 630012	630304 630012
Hexagon socket, 1/2 inch Width across flats 24 mm	642229 24
Hexagon socket, 1/2 inch Width across flats 30 mm	642229 30
Extension, 1/4 inch overall length 50 mm	632429 50
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631029 5,5
Universal joint, 1/2 inch Type 1/2	641629 1/2
Reversible ratchet, 1/2 inch with ejector Type	640025
Hexagon socket, 1/4 inch Width across flats 8 mm	631029 8
Hexagon socket, 1/4 inch Width across flats 11 mm	631029 11
Hexagon socket, 1/2 inch Width across flats 16 mm	642229 16
Hexagon socket, 1/4 inch Width across flats 9 mm	631029 9
Hexagon socket, 1/2 inch Width across flats 18 mm	642229 18
Modular box Type 4	630305 4
Hexagon bit socket, 1/4 inch long Hexagon 5 mm	631729 5
Extension, 1/4 inch overall length 150 mm	632429 150
Hexagon bit socket, 1/4 inch long Hexagon 4 mm	631729 4
Hexagon socket, 1/4 inch Width across flats 4 mm	631029 4
Extension, 1/2 inch overall length 130 mm	641029 130
T-handle, 1/2 inch overall length 295 mm	641329 295
Hexagon bit socket, 1/2 inch Hexagon 12 mm	643229 12
Hexagon socket, 1/4 inch Width across flats 5 mm	631029 5
Hexagon socket, 1/4 inch Width across flats 7 mm	631029 7
Reversible ratchet, 1/4 inch with ejector Type	632025
Hexagon socket, 1/2 inch Width across flats 27 mm	642229 27
Hexagon socket, 1/2 inch Width across flats 19 mm	642229 19

Hexagon bit socket, 1/2 inch Hexagon 8 mm	643229 8
Hexagon socket, 1/2 inch Width across flats 17 mm	642229 17
Hexagon socket, 1/2 inch Width across flats 13 mm	642229 13
Reversible ratchet, 1/2 inch with ejector Type 1/2	640025 1/2
Reversible ratchet, 1/4 inch with ejector Type 1/4	632025 1/4