

Garant
Socket set 1/4 inch square drive 13 pieces, Type: SD

Order data

Order number	630062 SD
GTIN	4062406060237
Item class	61A

Description
Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120.**

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay.**

Application:

For external hexagon screws / nuts with thread M2 – M8.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Sockets single hexagon: 9 pcs. No. 631225

size 4; 5; 5.5; 6; 7; 8; 10; 11; 13

Extensions "Wobble-Fix": 2 pcs. size 50, 150 mm

Universal joint: 1 pc. No. 633529 size 1/4

Ratchet: 1 pc. No. 632025 size 1/4

Storage in: ABS plastic box

Degree of fill of a drawer in units: 5x10

Height: 45 mm

Square drive: 1/4 in

Width across flats range, hexagon sockets: 4-13 mm

Technical description

Square drive	1/4 in
Drive profile	Hexagon socket
Width across flats range, hexagon sockets	4-13 mm
Hexagon socket profile	Surfacedrive
Square with Wobble-Fix	with angle of inclination
Material	Chrome vanadium steel
Packaging	ABS plastic box
Length	257 mm
Width	147 mm
Height	45 mm
Surface	chrome-plated
Degree of fill of a drawer in units	5×10
Type of product	Socket spanner

Accessories

Hexagon socket 1/4 inch Surface Drive Width across flats 13 mm	631225 13
Modular box Type 2	630305 2
Universal joint 1/4 inch Type 1/4	633529 1/4
Reversible ratchet, 1/4 inch with ejector Type	632025
Hexagon socket 1/4 inch Surface Drive Width across flats 11 mm	631225 11
Hexagon socket 1/4 inch Surface Drive Width across flats 7 mm	631225 7
PUR foam inlay for set 630062	630304 630062
Hexagon socket 1/4 inch Surface Drive Width across flats 10 mm	631225 10
Hexagon socket 1/4 inch Surface Drive Width across flats 5,5 mm	631225 5,5
	631225 5

Hexagon socket 1/4 inch Surface Drive Width across flats 5 mm

Hexagon socket 1/4 inch Surface Drive Width across flats 4 mm

631225 4

Hexagon socket 1/4 inch Surface Drive Width across flats 6 mm

631225 6

Hexagon socket 1/4 inch Surface Drive Width across flats 8 mm

631225 8

Reversible ratchet, 1/4 inch with ejector Type 1/4

632025 1/4