

Garant
Socket set 1/4; 1/2 inch square drive 65 pieces, Type: SD

Order data

Order number	630023 SD
GTIN	4062406060220
Item class	61A

Description
Version:

The Surface Drive profile works directly on the faces of the nuts and bolts; weaker corners are protected. Even intermediate sizes (e.g. inch size bolts) and worn bolt heads can be tightened or released using the Surface Drive profile. The Wobble-Fix extensions allow use at an angle and can be secured by clicking into place.

Drives / accessories to DIN 3122 / 3123;

sockets to DIN 3124. Internal / external square drives to DIN 3120.

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay**.

Application:

For external hexagon screws / nuts with thread M4 – M20 and for hexagon socket head screws with thread M4 – M18.

For Pozidriv and Phillips screws with threads M2 – M6, slot-head screws with thread M2.5 – M5, for internal Torx® screws with thread M3 – M8 and for Trisquare screws with thread M4 – M8.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

1/4 inch hexagon sockets, SurfaceDrive: 13 pcs. No. 631225 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14

1/2 inch hexagon sockets, Surface Drive: 12 pcs. No. 642325 size 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32; 34

1/2 inch hexagon screwdriver bits: 4 pcs. No. 643229 size 6; 8; 10; 14

1/4 inch hexagon BITS C 6.3: 4 pcs. similar to No. 675240 size 3; 4; 5; 6

1/4 inch BITS for Phillips C 6.3: 3 pcs. similar to No. 675310 size 1/25; 2/25; 3/25
 1/4 inch Pozidriv BITS C 6.3: 3 pcs. similar to No. 675320 size 1/25; 2/25; 3/25
 1/4 inch slot-head BITS C 6.3: 3 pcs. similar to No. 675250 size 3.5×0.6; 5.5×0.8; 8×1.2
 1/4 inch BITS for Torx® C 6.3: 6 pcs. similar to No. 675340 size TX10; TX15; TX20; TX25; TX30; TX40
 1/4 inch tri-square BITS C 6.3: 4 pcs. similar to No. 675565 size M4; M5; M6; M8
 1/4 inch tommy-bar: 1 pc. No. 633029 size 116
 1/4 inch spinner handle: 1 pc. No. 632829 size 1/4
 1/4 inch "Wobble-Fix" extensions: 2 pcs. No. 632519 size 50; 100
 1/2 inch extensions "Wobble-Fix": 1 pc. No. 641129 size 125
 1/4 inch universal joint: 1 pc. No. 633529 size 1/4
 1/2 inch universal joint: 1 pc. No. 641629 size 1/2
 1/4 inch ratchet: 1 pc. No. 632025 size 1/4 with ejector
 1/2 inch ratchet: 1 pc. No. 640025 size 1/2 with ejector
 1/4 inch adapter E 6.3: 1 pc. similar to No. 675020 6.3K for 1/4 inch BITS C 6.3
 1/4 inch converter: 1 pc. similar to No. 650005 size 2 hexagon coupling 1/4 inch E 6.3 – external square 1/4 inch
 1/2 inch converter: 1 pc. similar to No. 650005 size 5 hexagon coupling 7/16 inch E 11.2 – external square 1/2 inch
 1/4 inch bit adapter: 1 pc. similar to No. 676800 square socket 1/4 inch – bit holder 1/4 inch
 Presented in: ABS plastic box

Note:

The range offers in addition space for 4 pieces of small parts storage bins No. 951251 size 2×3/1 (not included in the scope of supply).

Technical description

Square drive	1/2 in
Square drive	1/4 in
Width across flats range, Surface Drive	4-34 mm
Width across flats range, hexagon wrenches	6-14 mm
Drive profile	Hexagon socket Surfacedrive
Drive profile	Hexagon screwdriver
Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver
Drive profile	Slot-head screwdriver
Drive profile	Screwdriver for TORX® screws
Drive profile	Tri-square screwdriver
Hexagon socket profile	Surfacedrive

Square with Wobble-Fix	with angle of inclination
Packaging	ABS plastic box
Length	510 mm
Width	294 mm
Height	61 mm
Degree of fill of a drawer in units	8×20
Type of product	Socket spanner

Accessories

Surface Drive hexagon socket, 1/2 inch Width across flats 19 mm	642325 19
Surface Drive hexagon socket, 1/2 inch Width across flats 32 mm	642325 32
T-handle, 1/4 inch overall length 116 mm	633029 116
Reversible ratchet, 1/4 inch with ejector Type	632025
Reversible ratchet, 1/2 inch with ejector Type	640025
Hexagon socket, 1/4 inch Surface Drive Width across flats 9 mm	631225 9
Universal joint 1/4 inch Type 1/4	633529 1/4
Hexagon socket, 1/4 inch Surface Drive Width across flats 12 mm	631225 12
Hexagon socket, 1/4 inch Surface Drive Width across flats 6 mm	631225 6
Hexagon socket, 1/4 inch Surface Drive Width across flats 4,5 mm	631225 4,5
Hexagon bit socket, 1/2 inch Hexagon 14 mm	643229 14
Hexagon socket, 1/4 inch Surface Drive Width across flats 10 mm	631225 10
Hexagon bit socket, 1/2 inch Hexagon 8 mm	643229 8
	631225 14

Hexagon socket, 1/4 inch Surface Drive Width across flats 14 mm	
Hexagon socket, 1/4 inch Surface Drive Width across flats 4 mm	631225 4
Surface Drive hexagon socket, 1/2 inch Width across flats 24 mm	642325 24
Surface Drive hexagon socket, 1/2 inch Width across flats 17 mm	642325 17
Universal joint, 1/2 inch Type 1/2	641629 1/2
Surface Drive hexagon socket, 1/2 inch Width across flats 15 mm	642325 15
Hexagon socket, 1/4 inch Surface Drive Width across flats 11 mm	631225 11
Hexagon bit socket, 1/2 inch Hexagon 6 mm	643229 6
Hexagon socket, 1/4 inch Surface Drive Width across flats 7 mm	631225 7
Surface Drive hexagon socket, 1/2 inch Width across flats 22 mm	642325 22
PUR foam inlay for set 630023	630304 630023
Surface Drive hexagon socket, 1/2 inch Width across flats 34 mm	642325 34
Surface Drive hexagon socket, 1/2 inch Width across flats 30 mm	642325 30
Surface Drive hexagon socket, 1/2 inch Width across flats 18 mm	642325 18
Surface Drive hexagon socket, 1/2 inch Width across flats 16 mm	642325 16
Hexagon socket, 1/4 inch Surface Drive Width across flats 5,5 mm	631225 5,5
Surface Drive hexagon socket, 1/2 inch Width across flats 27 mm	642325 27
Hexagon socket, 1/4 inch Surface Drive Width across flats 5 mm	631225 5
Surface Drive hexagon socket, 1/2 inch Width across flats 21 mm	642325 21

Hexagon socket, 1/4 inch Surface Drive Width across flats 8 mm	631225 8
Hexagon socket, 1/4 inch Surface Drive Width across flats 13 mm	631225 13
Modular box Type 4	630305 4
Hexagon bit socket, 1/2 inch Hexagon 10 mm	643229 10
Reversible ratchet, 1/4 inch with ejector Type 1/4	632025 1/4
Extension, 1/4 inch "Wobble-Fix" overall length 100 mm	632519 100
Spinner handle, 1/4 inch overall length 146 mm	632829 146
Reversible ratchet, 1/2 inch with ejector Type 1/2	640025 1/2
Extension, 1/2 inch "Wobble-Fix" overall length 125 mm	641129 125
Extension, 1/4 inch "Wobble-Fix" overall length 50 mm	632519 50