

**Garant**
**Socket set 1/2 inch square drive 35 pieces, Type: SD**

**Order data**

Order number	638025 SD
GTIN	4062406061401
Item class	61A

**Description**
**Version:**

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120.**

The Surface Drive profile works directly on the faces of the nuts and bolts; weaker corners are protected. Even intermediate sizes (e.g. inch size bolts) and worn bolt heads can be tightened or released using the Surface Drive profile. The Wobble-Fix extensions allow use at an angle and can be secured by clicking into place.

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay.**

**Application:**

For hexagon head screws / nuts with thread M5 – M22 and 1/4 – 7/8 inch (American inch size) and hexagon socket head screws with thread M5 – M18.

**Material:**

Chrome vanadium steel, chrome-plated.

**Supplied with:**

Hexagon sockets, Surface Drive: 19 pcs. No. 642325 size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32; 34

Hexagon screwdriver bits: 8 pcs. No. 643229 size 4; 5; 6; 7; 8; 10; 12; 14

T-handle: 1 pc. No. 641329 size 295

Extensions "Wobble-Fix": 2 pcs. No. 641129 size 125; 250

Universal joint: 1 pc. No. 641629 size 1/2

Ratchet: 1 pc. No. 640025 size 1/2

Converter: 1 pc. similar to No. 650002 size 5 drive input hexagon 7/16 inch E 11.2 - drive output square 1/2 inch

Adapters: 2 pcs. similar to No. 649500  
 drive input square socket 3/8 inch - drive output square 1/2 inch  
 drive input square socket 1/2 inch - drive output square 3/8 inch  
 Presented in: ABS plastic box

**Note:**

The range offers in addition space for 4 pieces of small parts storage bins No. 951251 size 2×3/1 or 2 pieces of small parts storage bins No. 951251 size 2×6/1 (not included in the scope of supply).

Degree of fill of a drawer in units: 8×20

Height: 61 mm

Square drive: 1/2 in

Width across flats range, Surface Drive: 8-34 mm

Width across flats range, hexagon wrenches: 4-14 mm

## Technical description

Width across flats range, Surface Drive	8-34 mm
Square drive	1/2 in
Number of pieces	35
Width across flats	metric
Width across flats range, hexagon wrenches	4-14 mm
Drive profile	Hexagon SurfaceDrive socket
Drive profile	Hexagon socket
Hexagon socket profile	Surfacedrive
Square with Wobble-Fix	with angle of inclination
Length	510 mm
Width	294 mm
Height	61 mm
Degree of fill of a drawer in units	8×20
Type of product	Socket spanner

## Accessories

Reversible ratchet, 1/2 inch with ejector Type	640025
--	--------

Surface Drive hexagon socket, 1/2 inch Width across flats 18 mm	642325 18
Surface Drive hexagon socket, 1/2 inch Width across flats 16 mm	642325 16
Surface Drive hexagon socket, 1/2 inch Width across flats 12 mm	642325 12
Universal joint, 1/2 inch Type 1/2	641629 1/2
Surface Drive hexagon socket, 1/2 inch Width across flats 11 mm	642325 11
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 10 mm	643229 10
easyPick small parts storage bins Height 50 mm Width×depth in G / type 2X3/1	951251 2X3/1
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 14 mm	643229 14
PUR foam inlay for set 638025	630304 638025
Surface Drive hexagon socket, 1/2 inch Width across flats 30 mm	642325 30
Surface Drive hexagon socket, 1/2 inch Width across flats 34 mm	642325 34
Modular box Type 4-1	630310 4-1
Surface Drive hexagon socket, 1/2 inch Width across flats 17 mm	642325 17
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 7 mm	643229 7
Modular box Type 4	630305 4
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 4 mm	643229 4
Surface Drive hexagon socket, 1/2 inch Width across flats 19 mm	642325 19
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 8 mm	643229 8
Surface Drive hexagon socket, 1/2 inch Width across flats 22 mm	642325 22

Surface Drive hexagon socket, 1/2 inch Width across flats 27 mm	642325 27
Surface Drive hexagon socket, 1/2 inch Width across flats 32 mm	642325 32
Surface Drive hexagon socket, 1/2 inch Width across flats 10 mm	642325 10
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 12 mm	643229 12
Surface Drive hexagon socket, 1/2 inch Width across flats 24 mm	642325 24
T-handle, 1/2 inch overall length 295 mm	641329 295
Surface Drive hexagon socket, 1/2 inch Width across flats 14 mm	642325 14
Surface Drive hexagon socket, 1/2 inch Width across flats 15 mm	642325 15
Surface Drive hexagon socket, 1/2 inch Width across flats 9 mm	642325 9
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 5 mm	643229 5
Surface Drive hexagon socket, 1/2 inch Width across flats 13 mm	642325 13
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 6 mm	643229 6
Surface Drive hexagon socket, 1/2 inch Width across flats 8 mm	642325 8
Surface Drive hexagon socket, 1/2 inch Width across flats 21 mm	642325 21