

 GRIDLINE

## Roller cabinet for drawers, 36×24G, Height mm / number of drawers: 860/0



### Order data

Order number	931327 860/0
GTIN	4062406063696
Item class	9GK

### Description

#### Version:

To take drawers 36×24G.

Roller cabinet in 40×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With anti-roll lip on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

Only No. 931354 or No. 931356 can be fitted with drawers (with one-hand individual drawer release system).

Material thickness: 1.2 mm

Drawer runner extension: Anti-tilt lock

Height adjustment interval: 25 mm

Cylinder lock: modular barrel

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 885 mm

Width: 1000 mm

Depth: 700 mm

Working height: 600 mm

Drawer body height: 700 mm

maximum load capacity: 600 kg

## Technical description

Weight	76 kg
Depth	700 mm
Drawer body height	700 mm
maximum load capacity	400 kg
Usable height	600 mm
Height	885 mm
Width	1000 mm
Wheel Ø	125 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×24G

## Accessories

Drawer with one-handed individual drawer locking, 75 kg Drawer front height 300 mm	931354 300
Drawer with one-handed individual drawer locking, 75 kg Drawer front height 75 mm	931354 75
Drawer with one-handed individual drawer locking, 75 kg Drawer front height 50 mm	931354 50
Drawer with one-handed individual drawer locking, 75 kg Drawer front height 125 mm	931354 125
Drawer with one-handed individual drawer locking, 75 kg Drawer front height 250 mm	931354 250

Drawer with one-handed individual drawer locking, 75 kg  
Drawer front height 100 mm

931354 100

Drawer with one-handed individual drawer locking, 75 kg  
Drawer front height 200 mm

931354 200

Drawer with one-handed individual drawer locking, 75 kg  
Drawer front height 150 mm

931354 150