

Garant GRIDLINE

**Base cabinet with Viewing window swing doors, Height: 1250mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 940863 1250   |
| GTIN         | 4062406070977 |
| Item class   | 9GI           |

**Description****Version:**

Empty cabinet in 50×20G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

|  |         |
|--|---------|
| Electronic locking system can be retrofitted | yes     |
| Width  | 1250 mm |
| Depth  | 500 mm  |
| Usable height                                | 1095 mm |

|  |  |
|--|--|
| Handle positioning                     | top  |
| Type of cabinet                        | Base cabinet   |
| Weight                                 | 91 kg  |
| Cabinet fronts                         | Viewing window swing door                                      |
| Height                                 | 1250 mm  |
| ComfortClose                           | no   |
| Depth in G                             | 20   |
| Width in G                             | 50   |
| Version                                | for individual configuration                                   |
| Material thickness                     | 0.9 mm   |
| Cabinet housing internal load capacity | 1000   |
| Door opening angle                     | 250 degrees  |
| Height adjustment interval             | 25   |
| Cylinder lock                          | modular barrel   |
| Colour selection                       | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product                        | Cabinet with shelves   |

## Accessories

|   |                  |
|---|------------------|
| Extended lighting set for GridLine cabinets with Swing doors, width 50G for cabinet height 1000/1250 mm | 940512 1000/1250 |
| Storage shelf slotted for cabinet / compartment width in G 50   | 940552 50        |
| Inclined shelf for cabinet / compartment width in G 50  | 940560 50        |
| Storage shelf 200 kg for cabinet / compartment width in G 50  | 940590 50        |
| Basic lighting set for GridLine cabinets with swing doors for cabinet height 1250 mm                    | 940501 1250      |
| Storage shelf for cabinet / compartment width in G 50   | 940550 50        |

Slide handle for GridLine Type GP11

914226 GP11