



Digital caliper IP67 with rod type depth gauge, Measuring range: 150 mm



Order data

Order number	412731 150
GTIN	4059192002428
Item class	43A

Description

Version:

Clearly legible, high-contrast LCD display. Waterproof inductive measurement system with reference-lock function. The measuring faces are precision lapped.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Packaging: sturdy box

Standard: DIN 862

Reversible reading: mm / inch

Depth gauge: \varnothing 1.5

IP Index of Protection: IP 67

Measured value saving: MAHR reference-lock system

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 inch

Error limit: 0.03 mm

Jaw length: 40 mm

Technical description

Reversible reading	mm / inch
Standard	DIN 862
Calibration	A1

Depth gauge available	yes
Depth gauge	Ø 1.5
Jaw length	40 mm
Scale divisions	0.01 mm
Scale divisions	0.0005 inch
Error limit	0.03 mm
Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Vernier caliper standard

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Plastic case Type MS150	412470 MS150
Plastic case Type MS150	412468 MS150