



### Hammer drill 230 V, Type: PLH32XE



#### Order data

Order number	075520 PLH32XE
GTIN	4002395233342
Item class	03M

#### Description

##### Version:

- **Sturdy hammer drill with pneumatic hammer action**
- **SDS plus chuck.**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**

**Mains combination hammer drill with high impact energy for drilling holes up to 32 mm in concrete.** Power cable 4 m.

- **FIXTEC tool quick-change system for switching between the SDS-Plus chuck and the quick-release metal drill chuck, without using tools.**
- **Zero rotation for easy chisel work.**
- **Safety clutch protects user and machine if the drill jams.**
- **AVS anti-vibration system.**

##### Advantage:

Anti-vibration system.

##### Supplied with:

FIXTEC SDS-plus adapter, quick-change chuck 1.5 – 13 mm, additional handle with depth stop, drilling grease, transport case.

##### Note:

Suitable carbide hammer drills can be found from No. 787000.

#### Technical description

## Data sheet

Power consumption	900 W
maximum twist drill size Ø in steel	16 mm
Quick-clamping chuck range	1.5 - 13 mm
maximum hammer rate	4500 - 4500 min <sup>-1</sup>
Manufacturer's designation	PLH32XE
maximum twist drill size Ø in wood	40 mm
Weight	3.6 kg
Tool arbor shape	SDS Plus
maximum vibration to EN	22 m/s <sup>2</sup>
Impact energy	3.8 J
maximum twist drill size Ø in concrete	32 mm
Speed range	0 - 800 min <sup>-1</sup>
Shank	SDS Plus
Packaging	Carrying case
Power supply	Mains operated
Suitable for material	Concrete
Suitable for material	Stone
Suitable for material	Masonry
Type of product	Hammer drill

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/075520-PLH32XE>