



Automotive Aftermarket Division

3M™ Scotch™ Tape 2328 Masking Tape

1) Part Numbers

06034 – 18mm x 50m
06309 – 24mm x 50m
06311 – 36mm x 50m
51286 – 48mm x 50m
51287 – 72mm x 50m

2) Description and end uses

Scotch™ Tape 2328 is a beige coloured masking tape developed specifically for the vehicle refinish industry, whilst being suitable for a wide variety of applications. It is compatible with a variety of substrates and all current refinish paint systems. Made from a crepe paper it offers excellent conformability and hold around corners, a secure grip and clean easy removal.

Sizes available:

Width (mm): 18, 24, 36, 48, 72.

Length (m): 50.

Features	Advantages	Benefits
Latex saturated creped	Conformability Thinness Solvent resistance Easy hand tear Good paint anchorage Sliver resistance	Good curve masking Good paint line Prevents paint bleed through Good handling Good paint flaking resistance Easy removal
Crosslinked rubber resin	Instant adhesion Good holding power	Sticks easily Resists lifting

3) Physical Properties

Thickness:	0.135 mm	AFERA 4006
Adhesion to steel:	6.5 N/25 mm	AFERA 4001
Tensile strength:	88 N/25 mm	AFERA 4004



Technical Data Sheet

Effective: 31/07/2019 Supersedes: 28/04/2008

4) Directions for Use

1. Ensure that the area/substrates to be masked is clean and dry prior to the application of the tape.

2. Window rubbers and plastic mouldings should be cleaned using a silicon remover / mild solvent to ensure they are free from contamination to improve the tapes adhesion.

3. If the tape has been baked and left overnight allowing it to go cold and damp, we recommend the vehicle be warmed prior to the tape removal. Failure to do so may result in adhesive residue being left on the vehicle.

Satisfactory performance and clean removal of Scotch™ Tape 2328 will be achieved at varying temperatures/time exposure on many substrates. Tests should be conducted to establish Scotch™ Tape 2328 performance parameters in your process conditions. The optimum level for product performance and easy removal is at 80 °C for 60 min.

5) Storage

Store in clean dry place. Temperature of 21°C and 50 percent relative humidity are recommended.

6) Safety

3M™ Automotive Aftermarket Products are designed FOR PROFESSIONAL USE ONLY.

Always use the product in the manner in which it is designed to be used. When using solvents etc. for cleaning the surface prior to the SEMFT application, care must be taken to avoid contact with the skin and eyes. The correct PPE must be worn at all times

When removing the masking tape after use from the vehicle it should be disposed of following local authority/ country guidelines.



Technical Data Sheet

Effective: 31/07/2019 Supersedes: 28/04/2008

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.

For Additional Health and Safety Information

<p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391</p> <p>aadenquiries.uk@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Ireland Limited Automotive Aftermarket The Iveagh Building The Park Carrickmines Dublin 18 Tel: +353 12160301</p> <p>aadenquiries.uk@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100</p> <p>3mkundeservicedk@mmm.com www.3MAuto.dk</p>
<p>3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1</p> <p>tilaukset@mmm.com www.3M.fi/autotuotteet</p>	<p>3M Svenska AB Automotive Aftermarket Bileftermarknad 19189 Sollentuna Tel: 08-922100</p> <p>kundservice@mmm.com www.3M.se/bileftermarkad</p>	<p>3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384</p> <p>kundeservice@mmm.com www.3m.no/auto</p>
<p>3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120</p> <p>www.3m.lv</p>	<p>3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902</p> <p>www.3m.ee</p>	<p>3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780</p> <p>www.3m.lt</p>
<p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391</p> <p>aadenquiries.uk@mmm.com</p>	<p>3M Ireland Limited Automotive Aftermarket The Iveagh Building The Park Carrickmines Dublin 18 Tel: +353 12160301</p> <p>aadenquiries.uk@mmm.com</p>	<p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100</p> <p>3mkundeservicedk@mmm.com</p>



Technical Data Sheet

Effective: 31/07/2019 Supersedes: 28/04/2008

www.3Mbodyshop.co.uk	www.3Mbodyshop.co.uk	www.3MAuto.dk
3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1 tilaukset@mmm.com www.3M.fi/autotuotteet	3M Svenska AB Automotive Aftermarket Bileftermarknad 19189 Sollentuna Tel: 08-922100 kundservice@mmm.com www.3M.se/bileftermarkad	3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 kundeservice@mmm.com www.3m.no/auto
3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120 www.3m.lv	3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 www.3m.ee	3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 www.3m.lt

© 3M 2019. 3M and Scotch are trademarks of the 3M company. All rights reserved