



Technical Data Sheet

Effective: 29/05/2019 Supersedes: 25/03/2016

Automotive Aftermarket Division

3M™ Flexible Abrasive Hookit™ Sheets

1) Part Numbers

34337	:	P400
34339	:	P600
34340	:	P800
34341	:	P1000
34342	:	P1200
34343	:	P1500

34352 : Flexible abrasive foam pad

2) Description and end uses

Flexible coated abrasive sheet for abrasion of Lacquers, paints, plastics and polyester fillers/primers.

3) Physical Properties

Mineral	:	Aluminium Oxide
Coating	:	Closed Coat
Bonding	:	Resin Bond
Colour	:	Green (P400 – P600) Brown (P800 – P1000) Purple (1200 – P1500)
Grades	:	P400 – P1500 (FEPA)

4) Directions for Use

Flexible, conformable abrasive sheet for improved access to awkward areas. Ideal for shaping and feather edging. Ideal for hand sanding applications for critical or awkward areas such as headlight openings, around door handles, door jambs, etc. Helps to eliminate finger marks and can be used wet or dry.



Technical Data Sheet

Effective: 29/05/2019 Supersedes: 25/03/2016

5) Storage

It is recommended that all Coated Abrasive Products should be stored at constant levels of temperature and humidity within the ranges of 18-22°C, 50-65% RH. They should be kept away from damp (or cold) walls, windows or floors to avoid possible moisture absorption. Equally storage adjacent to heat sources e.g. steam pipes, radiators, hot air ducts, ovens, etc. should be avoided.

Product is best stored in original packaging until ready for use. Shelf Life indefinite under these conditions.

6) Safety

Whenever possible, sanding should be carried out in a well ventilated area and it is strongly recommended that suitable goggles, dust mask and gloves are worn.

Pads should not be modified in any way. They should be used only in their original size and shape, as supplied.

3M™ Flexible Abrasive Hookit™ Sheets are designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Technical Data Sheet

Effective: 29/05/2019 Supersedes: 25/03/2016

For Additional Health and Safety Information

<p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391</p> <p>aadenquiries.uk@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Ireland Limited Automotive Aftermarket The Iveagh Building The Park Carrickmines Dublin 18 Tel: +353 12160301</p> <p>aadenquiries.uk@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100</p> <p>3mkundeservicedk@mmm.com www.3MAuto.dk</p>
<p>3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1</p> <p>tilaukset@mmm.com www.3M.fi/autotuotteet</p>	<p>3M Svenska AB Automotive Aftermarket Bileftermarknad 19189 Sollentuna Tel: 08-922100</p> <p>kundservice@mmm.com www.3M.se/bileftermarkad</p>	<p>3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384</p> <p>kundeservice@mmm.com www.3m.no/auto</p>
<p>3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120</p> <p>www.3m.lv</p>	<p>3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902</p> <p>www.3m.ee</p>	<p>3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780</p> <p>www.3m.lt</p>

© 3M 2019. 3M and Hookit are trademarks of the 3M company. All rights reserved