



Automotive Aftermarket Division

3M™ Softback Sanding Sponges

1) Part Numbers

Available in different grits/grades and sizes.

2) Description and end uses

Colour coded for easy identification.

3) Physical Properties

115 mm x 140 mm

Backing: Polyurethane Foam

Mineral: Aluminium Oxide

4) Directions for Use

Medium	-	After Filler preparation
Fine	-	E – Coat Sanding
Superfine	-	Primer sanding (awkward areas)
Ultrafine	-	Primer sanding (awkward areas, critical colours)
Microfine	-	De-nib base coat, prep blending (awkward areas)

Flexible, conformable foam pad for improved access to awkward areas. Ideal for shaping and feather edging. Ideal for hand sanding applications for critical or awkward areas such as headlight openings, around door handles, door jambs, etc. Helps to eliminate finger marks and can be used wet or dry.

5) Storage

It is recommended that all Coated Abrasive products should be stored at constant levels of temperature and humidity within the ranges of 18-22°C, 50-65% RH. They should be kept away from damp (or cold) walls, windows or floors to avoid possible moisture absorption. Equally storage adjacent to heat sources e.g. steam pipes, radiators, hot air ducts, ovens, etc., should be avoided.



Technical Data Sheet

Effective: 31/07/2019 Supersedes: 27/10/08

Product is best stored in original packaging until ready for use. Shelf life indefinite under these conditions.

6) Safety

7)

Whenever possible, sanding should be carried out in a well-ventilated area and it is strongly recommended that suitable goggles, dust mask and gloves are worn.

3M™ Softback Sanding Sponges is designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

8) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.

For Additional Health and Safety Information

3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadenquiries.uk@mmm.com www.3Mbodyshop.co.uk	3M Ireland Limited Automotive Aftermarket The Iveagh Building The Park Carrickmines Dublin 18 Tel: +353 12160301 aadenquiries.uk@mmm.com www.3Mbodyshop.co.uk	3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 3mkundeservicedk@mmm.com www.3MAuto.dk
3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1 tilaukset@mmm.com www.3M.fi/autotuotteet	3M Svenska AB Automotive Aftermarket Bileftermarknad 19189 Sollentuna Tel: 08-922100 kundservice@mmm.com www.3M.se/bileftermarkad	3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 kundeservice@mmm.com www.3m.no/auto
3M Latvija K.Ulmana 5 Rīga, LV-1004	3M Eesti OU Pärnu mnt. 158 11317 Tallinn	3M Lietuva A.Goštauto str. 40 A



Technical Data Sheet

Effective: 31/07/2019 Supersedes: 27/10/08

Tel: +371 67066120 www.3m.lv	Tel: +372 6 115 902 www.3m.ee	LT-01112 Vilnius Tel: +370 5 2160780 www.3m.lt
--	---	---

© 3M 2019. 3M is a trademark of the 3M company. All rights reserved