


**Transport equipment**

# Product data sheet

Article no.: 12505 Open cart



Modular System: The Super-Multivario-Transporter is especially designed for heavy loads. High-quality elasticated solid-rubber wheels and hubs with ball bearings guarantee an extreme manoeuvrability and a smooth run. Steel tube and sectional steel welded, powder coated, blue RAL 5007. Platforms and 1 end made of antislip waterproof plywood boards (insert type of board). 2 swivel and 2 fixed-wheel castors, elasticated solid rubber tyres, blue-grey "trackless", hubs with ball bearings. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



|  |                                |
|--|--------------------------------|
| <b>Total load capacity (kg)</b>        | 1200                           |
| <b>Length of usable platform (mm)</b>  | 1600                           |
| <b>Width of usable platform (mm)</b>   | 800                            |
| <b>Height of loading platform (mm)</b> | 283                            |
| <b>Total length (mm)</b>               | 1755                           |
| <b>Total width (mm)</b>                | 800                            |
| <b>Total height (mm)</b>               | 283                            |
| <b>Tyres</b>                           | Elastic solid rubber blue grey |
| <b>Wheel size (mm)</b>                 | 200 x 50                       |
| <b>Weight (kg)</b>                     | 60                             |
| <b>Country of origin</b>               | Germany                        |
| <b>Warranty (years)</b>                | 10                             |
| <b>Customs tariff number</b>           | 87168000                       |
| <b>GTIN</b>                            | 4017976125053                  |