


Transport equipment

Product data sheet

Article no.: 11051 Truck for appliances



Truck for appliances eases the transport of heavy equipment on flat surfaces and particularly on stairs. Welded steel tube construction, powder coated, blue RAL 5007. Wide rubber pads and non-slip cover on the blades. Wheel hubs with roller bearings. Features: large pneumatic tyres, solid rubber support wheels 160 x 40 mm, "trackless" (This makes the truck easy to move when lowered.), wheel locks on the support wheels (enabling these to be used as brakes when negotiating stairs.), the handlebar is height adjustable and can be turned through 180° (enabling it to be properly adjusted for any transport situation), tension belt to secure the load.

Technical Details:



Total load capacity (kg)	400
Blade width (mm)	550
Blade depth (mm)	190
Total width (mm)	700
Total height (mm)	1300
Tyres	Pneumatic
Wheel size (mm)	300 x 100
Weight (kg)	39
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976110509