


Transport equipment

Product data sheet

Article no.: 1384 Euro box cart



Modular system: Tubular and sectional steel construction, bolted, powder coated blue RAL 5007. Variable use of shelf frames, distance 150 mm, angle when inclined 15° and 30°. With 5 platforms made of derived timber material boards, rim 10 mm high. 4 swivel castors with TPE tyres, hubs with groove ball bearing. 2 Swivel castors with wheel locks, according to European Standard EN1757-3 (safety of platform trolleys). Capacity upper and middle shelves 80 kg.

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	1240
Width of usable platform (mm)	610
Shelf heights (mm)	311, 611, 911, 1211, 1511
Load capacity per shelf (kg)	80
Total length (mm)	1372
Total width (mm)	685
Total height (mm)	1686
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	109
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976013848