


Transport equipment

Product data sheet

Article no.: 1158 Dolly with gooseneck handle



Made of tubular steel welded and powder coated, blue RAL 5007, with wooden platform, handles bolted on. 1 swivel castor and 2 fixed-wheel castors. Wheels with TPE tyres, hubs with precision deep groove ball bearing. Swivel castor with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



| | |
|--|---------------|
| Total load capacity (kg) | 200 |
| Length of usable platform (mm) | 600 |
| Width of usable platform (mm) | 450 |
| Height of loading platform (mm) | 195 |
| Total length (mm) | 860 |
| Total width (mm) | 450 |
| Total height (mm) | 860 |
| Tyres | TPE |
| Wheel size (mm) | 125 x 32 |
| Weight (kg) | 10 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976011585 |