


**Transport equipment**

# Product data sheet

Article no.: 18202 Shelved trolley



Modular System: The Super-Multivario-Transporter is especially designed for heavy loads. High-quality elasticated solid-rubber wheels and hubs with ball bearings guarantee an extreme manoeuvrability and a smooth run. Steel tube and sectional steel welded, powder coated, blue RAL 5007. 1 fix and 3 variable shelves made of waterproof stable plywood boards. 1 side anti-slip the other side smooth. Variable use of shelves, minimum distance 100 mm. Capacity per shelf 180 kg. 2 swivel and 2 fixed-wheel, elasticated solid rubber tyres blue-grey "trackless", hubs with ball bearings. Castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	1200
<b>Load capacity per shelf (kg)</b>	180
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	700
<b>Total length (mm)</b>	1173
<b>Total width (mm)</b>	700
<b>Total height (mm)</b>	1583
<b>Shelf heights (mm)</b>	283, 688, 1088, 1488
<b>Tyres</b>	Elastic solid rubber blue grey
<b>Wheel size (mm)</b>	200 x 50
<b>Weight (kg)</b>	85
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976182025