


Transport equipment

Product data sheet

Article no.: 12405/7016 Table top cart "GREY EDITION"



Modular System: The Super-Multivario-Transporter is especially designed for heavy loads. High-quality elasticated solid-rubber wheels and hubs with ball bearings guarantee an extreme manoeuvrability and a smooth run. Steel tube and sectional steel welded, powder coated, anthracite grey RAL 7016. 2 platforms made of antislip waterproof plywood boards (insert type of board). 2 swivel and 2 fixed-wheel castors, elasticated solid rubber tyres, blue-grey "trackless", hubs with ball bearings. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper platform 500 kg.

Technical Details:



Total load capacity (kg)	1200
Length of usable platform (mm)	1600
Width of usable platform (mm)	800
Shelf heights (mm)	283, 925
Total length (mm)	1810
Total width (mm)	800
Total height (mm)	925
Tyres	Elastic solid rubber blue grey
Wheel size (mm)	200 x 50
Weight (kg)	100
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976819181