


Transport equipment

Product data sheet

Article no.: 2016 Mobile drum cradle



For transporting, storing and draining of 200-litre drums. Tubular steel construction, bolted, powder coated blue RAL 5007. Tension belt to secure the drums. Flat packed for easy self assembly. Fully-fledged mobile drum cradle with lever handle, mobile. With rollers for turning the drums. Applying the drums without lever handle. 2 polyamide castor wheels 125 x 38 mm and 2 polyamide wheels 150 x 40 mm. Castor wheels with wheel lock. With 2 steel rolls 50 mm Ø and 50 mm long. For easy turning of drums. Particularly suitable for thin walled drums.

Technical Details:



Total load capacity (kg)	250
Total width (mm)	615
Total height (mm)	600
Tyres	Polyamide
Wheel size (mm)	150 x 40 125 x 38
Weight (kg)	24
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976820163