


Transport equipment

Product data sheet

Article no.: 22801 Pallet dolly



For pallets and boxes. Sturdy sectional steel construction with 4 catch corners for stacking, powder coated. 2 swivel and 2 fixed-wheel castors. Swivel castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). TPE tyres 200 x 40 mm, hubs with groove ball bearing. Very low starting, rolling and swivelling resistance. Tyres are non-marking (trackless). Low-noise running on even flooring. Optional extras are only delivered in a set with pallet dollies because they are welded together.

Technical Details:



Total load capacity (kg)	750
Length of usable platform (mm)	1210
Width of usable platform (mm)	810
Height of loading platform (mm)	282
Total length (mm)	1255
Total width (mm)	855
Total height (mm)	329
Tyres	TPE
Wheel size (mm)	200 x 40
Version	for euro pallets
Weight (kg)	34
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976228013