


Transport equipment

Product data sheet

Article no.: 12452/7016 Steel sheet workshop cart "GREY EDITION"



Made of steel sheets with 1 cupboard, 1 fixed and 2 adjustable shelves, and 4 drawers (4 drawers H x W x D: 1 pc. 105 x 280 x 470 mm, 2 pcs. 160 x 280 x 470 mm, 1 pc. 210 x 280 x 470 mm) with sliding guide. Centrally lockable by cylinder lock. Powder coated, carcass grey RAL 7035, front anthracite grey RAL 7016. Worktop composite panel grey 20 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	985
Width of usable platform (mm)	590
Height of loading platform (mm)	915
Total length (mm)	1080
Total width (mm)	590
Total height (mm)	995
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	67
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976624525