


Transport equipment

Product data sheet

Article no.: 22812 Pallet dolly



For pallets and boxes. Sturdy sectional steel construction with 4 catch corners for stacking, powder coated. 2 castor wheels and 2 fixed wheels 200 x 50 mm. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Elasticated solid rubber tyres, blue-grey "trackless", hubs with ball bearings. Low rolling resistance, easy movement, no road noise. Optional extras are only delivered in a set with pallet dollies because they are welded together.

Technical Details:



Total load capacity (kg)	1200
Length of usable platform (mm)	1210
Width of usable platform (mm)	1010
Height of loading platform (mm)	282
Total length (mm)	1255
Total width (mm)	1055
Total height (mm)	329
Tyres	Elastic solid rubber blue grey
Wheel size (mm)	200 x 50
Version	for industrial pallets
Weight (kg)	36
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976228129