


**Transport equipment**

# Product data sheet

Article no.: 23799 ESD-pallet dolly



Pallet dollies for pallets and lattice boxes. Sturdy sectional steel construction with 4 catch corners for stacking. Tubular steel and sectional steel welded, conductive powder coating, slate grey, RAL 7015. Screw and plug type construction. 2 swivel and 2 fixed-wheel castors with TPE-ESD tyres (thermoplastic elastomer), electrically conductive. Hubs with precision groove ball bearing. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are nonmarking.

## Technical Details:



<b>Total load capacity (kg)</b>	750
<b>Length of usable platform (mm)</b>	810
<b>Width of usable platform (mm)</b>	610
<b>Height of loading platform (mm)</b>	282
<b>Total length (mm)</b>	855
<b>Total width (mm)</b>	655
<b>Total height (mm)</b>	329
<b>Tyres</b>	TPE-ESD
<b>Wheel size (mm)</b>	200 x 40
<b>Version</b>	for industrial pallets
<b>Weight (kg)</b>	30
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976237992