


Transport equipment

Product data sheet

Article no.: 2380 Euro box cart



Tubular and sectional steel construction, bolted, powder coated. Open frame. Variable use of shelf frames, distance 50 mm, angle when inclined up to 15° and 30°. 4 swivel castors with TPE tyres, hubs with groove ball bearing. 2 Swivel castors with wheel locks, according to European Standard EN1757-3 (safety of platform trolleys). Capacity upper and middle shelves 80 kg.

Technical Details:



| | |
|---------------------------------------|---------------|
| Total load capacity (kg) | 250 |
| Length of usable platform (mm) | 410 |
| Width of usable platform (mm) | 610 |
| Shelf heights (mm) | 238, 538, 838 |
| Load capacity per shelf (kg) | 80 |
| Total length (mm) | 525 |
| Total width (mm) | 666 |
| Total height (mm) | 1101 |
| Tyres | TPE |
| Wheel size (mm) | 125 x 32 |
| Weight (kg) | 27 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976023809 |