


Transport equipment

Product data sheet

Article no.: 1600 Table top cart



Modular system, platform and pushbar with screw connection, upper shelves can be inserted. Capacity upper shelf 80 kg. Disassembled on delivery. Welded tubular or sectional steel construction, powder coated, blue RAL 5007. Shelves made of derived timber material board, beech decor surface. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	200
Length of usable platform (mm)	850
Width of usable platform (mm)	500
Shelf heights (mm)	209, 826
Total length (mm)	1030
Total width (mm)	500
Total height (mm)	1020
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	25
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976016009