


Transport equipment

Product data sheet

Article no.: 1820 ESD-dolley with gooseneck handle



Made of tubular steel welded, handle bolted on. Electrostatic discharge construction, conductive powder coating, slate grey, RAL 7015. 2 electrically conductive wooden shelves according to DIN 68765, light grey. Capacity of upper shelf 100 kg.

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	600
Width of usable platform (mm)	450
Total length (mm)	860
Total width (mm)	450
Total height (mm)	875
Tyres	TPE-ESD
Wheel size (mm)	125 x 32
Weight (kg)	15
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976491820