


Transport equipment

Product data sheet

Article no.: 1841 ESD-table top cart



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey. Screw and plug type construction. 2 electrically conductive wooden shelves according to DIN 68765, light grey. 2 swivel and 2 fixed-wheel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity of upper shelf 80 kg.

Technical Details:



Total load capacity (kg)	300
Length of usable platform (mm)	1000
Width of usable platform (mm)	600
Shelf heights (mm)	206, 827
Total length (mm)	1136
Total width (mm)	611
Total height (mm)	1039
Tyres	TPE-ESD
Wheel size (mm)	125 x 32
Weight (kg)	39
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976018416