


Transport equipment

Product data sheet

Article no.: 2437 Workshop cart with skirting



Modular system: Workshop cart in sectional/ tubular steel construction, powder-coated, blue RAL 5007. Surface out of beech plywood, 22 mm thick with skirting on 3 sides, 80 mm high. 1 additional shelf and 1 centrally lockable cupboard of drawers, 3 drawers 120 mm high and 1 drawer 180 mm high. Ball pull-out and pull-out lock. 4/5-pull-out. 500 mm wide, 600 mm deep and 600 mm high. Powder coated, grey carcass RAL 7035, blue front RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	1120
Width of usable platform (mm)	650
Shelf heights (mm)	226, 537, 850
Total length (mm)	1220
Total width (mm)	650
Total height (mm)	930
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	86
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976024370