


**Transport equipment**

# Product data sheet

Article no.: 1891 ESD-mobile tilting stand



Electrostatic discharge construction. For plastic boxes, steel plate boxes, wire baskets etc., adjustable in height and mobile. Sectional steel-/ tubular construction with steel plate platform with single sided lay-on edge, inclinable by 15° und 30°, adjustable in height in intervals of 25 mm. Powder coating, slate grey RAL 7015. 4 swivel castors with TPE-ESD tyres, hubs with slide bearing. Brakes at 2 swivel castors according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	150
<b>Length of usable platform (mm)</b>	510
<b>Width of usable platform (mm)</b>	410
<b>Angle of inclination (degree)</b>	0, 15, 30
<b>Height adjustable from-to (mm)</b>	500-775
<b>Tyres</b>	TPE-ESD
<b>Wheel size (mm)</b>	75 x 25
<b>Weight (kg)</b>	17,6
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	94032080
<b>GTIN</b>	4017976018911