


Transport equipment

Product data sheet

Article no.: 2102 Storeroom trolley



Tubular steel, welded construction, powder coated, blue RAL 5007. Platform made of derived timber material board, beech decor surface. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	1000
Width of usable platform (mm)	700
Height of loading platform (mm)	233
Total length (mm)	1180
Total width (mm)	705
Total height (mm)	953
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	29
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976021027