


Transport equipment

Product data sheet

Article no.: 2200 Electric drive unit



Electric drive as a fit-on unit for all pushbar carts, openside platform carts, box carts, table top carts, shelved carts etc. with a wheel-Ø of 200 mm and width from 500 mm. Drive complete with batteries and charging device. Compact unit, easily to be assembled. Operating switch to be clamped to pushbar, connection with plug-in helix cable. Speed fully adjustable, for forward and reverse gears. Technical specifications: Drive unit: 24 V DC 2 PM motors: 2 x 12 V, 250 W, 0,7 HP 2 GEL batteries: 2 x 12 V, 33 Ah, maintenance free. Max. speed 4,8 km/h, with fully charged batteries on a flat surface and a load of 500 kg, max. range: approx.15 km. Hill climbing ability with 500 kg load: 5%/2° Elasticated solid-rubber tyres 200 x 50 mm, blue-grey, trackless. Guarantee: 12 months Additional charge per

Technical Details:



Total load capacity (kg)	500
Note	surcharge - no single sale
Weight (kg)	55
Country of origin	Germany
Warranty (years)	1
Customs tariff number	87168000
GTIN	4017976322001