


Transport equipment

Product data sheet

Article no.: 2402-IS1 Table top cart with equipment for infection protection



Modular system: Tubular steel and sectional steel, welded and powder coated, surface durably protected, resistant to impact and scratches. 2 shelves made of derived timber material boards, surface beech grain. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper shelf 200 kg. Also equipped with infection protection frame 5901, disinfectant holder 1393-B0500 (for 500 ml Bode bottle) and spray bottle holder 1391. Bottles not included in the delivery.

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1000
Width of usable platform (mm)	700
Shelf heights (mm)	270, 900
Total length (mm)	1197
Total width (mm)	758
Total height (mm)	2010
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	60,2
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976202402