


Transport equipment

Product data sheet

Article no.: 2420 Heavy table top cart



Modular system: Tubular steel and sectional steel, welded and powder coated, surface durably protected, resistant to impact and scratches. 3 shelves made of derived timber material boards, surface beech grain. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper and middle shelf 200 kg.

Technical Details:



Total load capacity (kg)	500
Length of usable platform (mm)	850
Width of usable platform (mm)	500
Shelf heights (mm)	228, 544, 860
Total length (mm)	1047
Total width (mm)	509
Total height (mm)	860
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	50
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976024202